



The new halogen reflector – a spot of crisp white light

Halogen Twist GU10

Mains-voltage halogen in glass reflector. Ideal solution for small decorative luminaires, putting your objects in a superior-quality spot light. Aluminum coating reduces heat in the backlight.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement costs due to longer burning hours

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Aluminum coating
- Universal burning position
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


Halogen Twist GU10

Versions



GU10, MR16

Dimensional drawing



Product	D (max)	C (max)
Halogen Twist 35W GU10 230V 40D 1CT/10X5F	50.7 mm	51 mm

