



# The new classic light bulb

## Halogen Classic P45

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Benefits

- Sparkling, crisp white halogen light of professional quality
- 30% energy savings compared with standard incandescent lamps
- Excellent colour rendering
- Creates an attractive ambiance
- Dimmable

### Features

- Superior quality of light with excellent colour rendering ( $R_a \geq 100$ )
- Mains-voltage lamp, no transformer needed
- Universal burning position
- Instant start

### Application


- Accent and general lighting applications in homes, offices, shops, hotels and restaurants. Replacement for traditional bulb in classical luminaires

# Halogen Classic P45

## Versions



## Dimensional drawing



Product	D (max)	C (max)
ClassicHalo 30 28W B22 240V P45 CL 2PF	46 mm	72.5 mm

