

Product Description

HF-PERFORMER για κυκλικούς λαμπτήρες TL5

Compact, square, lightweight, High Frequency electronic ballasts for TL5 Circular lamps

Οφέλη

- 50% longer lamp life than with conventional ballasts
- Up to 25% energy saving at constant luminous flux compared with conventional ballasts
- Constant light independent of mains voltage fluctuations

Χαρακτηριστικά


- Programmed start: flicker-free, warm-start circuit
- Protected against excessive mains voltages
- Automatic stop circuit (safety stop) is activated within 5 seconds in case of lamp failure; ballast resets automatically after lamp replacement

Εφαρμογή


- Ideal for commercial indoor lighting applications where it is necessary to reduce the wattage per square meter or operating costs
- Used with movement-detection control systems like Philips OccuPlus
- Mainly for indoor applications such as spotlights, downlights and recessed fixtures used primarily in retail stores, office buildings, supermarkets, hotels and convenience stores

HF-PERFORMER για κυκλικούς λαμπτήρες TL5

Versions



Σχεδιάγραμμα διαστάσεων



Product	D1	C1	A1	A2	B1	B2
HF-P 160 TL5C 220-240V 50/60Hz	4.5 mm	30.0 mm	103.0 mm	93.5 mm	67.0 mm	57.5 mm

