



# Product Description

## HalogenA IDE

Mains-voltage high-wattage double-envelope giving a white halogen light

### 优点

- Bright, sparkling halogen light
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Low replacement costs due to long lifetime

### 特点

- Quartz burner with a linear tungsten filament in a single-ended thermal-shock-resistant clear glass tubular envelope
- High luminous efficacy
- Excellent color rendering


### 应用

- Typical application: outdoor floodlighting such as sport grounds, car parks, building sites, harbours and airport aprons
- Also used in Indoor applications: public halls, factories, sport halls etc.

## Versions



二维绘图



Product
HalogenA IDE 1000W E40 230V CL 1CT/6

