



EnduraBay HPK238

EnduraBay HPK138/238

HPK238's attractive and unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. Its robust, dependable construction along with its ease of installation and maintenance truly make this highbay luminaire a durable, yet appealing solution. EnduraBay LX HPK138 Elegance and efficiency were the themes driving the design of EnduraBay LX. Its attractive yet unobtrusive presence energizes your interior surroundings, assuring you functionality, safety and overall product performance. What's more, it is easy on your budget. EnduraBay LX truly offers you peace of mind in your highbay installation. This robust luminaire makes it an impressive light source, as does its attractive minimalist design. The most striking feature of this high-bay luminaire is its four "shields" on the upper part of the housing, giving any lighting installation a distinctive elegance.

Features

- HPK238
- Attractive outlook with a tangible product quality
- Good light performance with more options for lamp & optics choices
- Designed for safety and durability
- Easy to install and maintain
- Reliable ingress protection
- Easy to specify
- HPK138
- The grooves divide the skin of the cylinder in four robust looking 'shields' which extend beyond the top and bottom of the gear housing, giving a touch of elegance to the luminaire's unique appearance
- For ease of installation. It is equipped with an external mains entry cable, therefore no access is required into the main body of the fitting saving labor and time
- Re-lamping is simple and does not require the use of any tools or the dismantling of any parts"

EnduraBay HPK138/238

Application

- General industry
- Logistic centers and warehouses
- Power plants
- Public areas

Versions



General Information

Cap-Base	E40
Protection class IEC	Safety class I

Operating and Electrical

Order Code	Full Product Name	Maximum lamp	
		Input Voltage	power
911401092880	HPK238 1xHPI-P250W-BU IC 220 50 BK	220 V	-
911401092980	HPK238 1xHPI-P400W-BUS IC 220 50 BK	220 V	-
911401093480	HPK238 1xHPL-N250W IC 220V-60Hz BK	220 V	-
911401093580	HPK238 1xHPL-N400W IC 220V-60Hz BK	220 V	-
911401093680	HPK238 1xHPI-P250W-BU IC 220 60 BK	220 V	-
911401093880	HPK238 1xSON150W IC 220V-60Hz BK	220 V	-
911401093980	HPK238 1xSON250W IC 220V-60Hz BK	220 V	-
911401094280	HPK238 1xHPL-N250W IC 230 50 BK	230 V	-
911401094380	HPK238 1xHPL-N400W IC 230 50 BK	230 V	-

Order Code	Full Product Name	Maximum lamp	
		Input Voltage	power
911401094480	HPK238 1xHPI-P250W-BU IC 230 50 BK	230 V	-
911401094580	HPK238 1xHPI-P400W-BUS IC 230 50 BK	230 V	-
911401094680	HPK238 1xSON150W IC 230 50 BK	230 V	-
911401094980	HPK238 1xHPI-P250W-BU IC 240V-50Hz BK	240 V	-
911401095080	HPK238 1xHPI-P400W-BUS IC 240 50 BK	240 V	-
911401095180	HPK238 1xSON150W IC 240 50 BK	240 V	-
911401095280	HPK238 1xSON250W IC 230/240 50 BK	230 to 240 V	-
911401095380	HPK238 1xSON400W IC 230/240 50 BK	230 to 240 V	-
911401096280	HPK238 MAX250W-E40 E	-	Max. 250 W

General Information

Order Code	Full Product Name	Compensation circuit	Gear	Lamp family code	Lamp power	Number of light sources	Lamp system description
911401092880	HPK238 1xHPI-P250W-BU IC 220 50 BK	Inductive parallel compensated	CONV	HPI-P	250 W	1 pc	Base-Up
911401092980	HPK238 1xHPI-P400W-BUS IC 220 50 BK	Inductive parallel compensated	CONV	HPI-P	400 W	1 pc	Base-Up/internal Starter
911401093480	HPK238 1xHPL-N250W IC 220V-60Hz BK	Inductive parallel compensated	CONV	HPL-N	250 W	1 pc	-
911401093580	HPK238 1xHPL-N400W IC 220V-60Hz BK	Inductive parallel compensated	CONV	HPL-N	400 W	1 pc	-
911401093680	HPK238 1xHPI-P250W-BU IC 220 60 BK	Inductive parallel compensated	CONV	HPI-P	250 W	1 pc	Base-Up
911401093880	HPK238 1xSON150W IC 220V-60Hz BK	Inductive parallel compensated	CONV	SON	150 W	1 pc	-
911401093980	HPK238 1xSON250W IC 220V-60Hz BK	Inductive parallel compensated	CONV	SON	250 W	1 pc	-
911401094280	HPK238 1xHPL-N250W IC 230 50 BK	Inductive parallel compensated	CONV	HPL-N	250 W	1 pc	-
911401094380	HPK238 1xHPL-N400W IC 230 50 BK	Inductive parallel compensated	CONV	HPL-N	400 W	1 pc	-
911401094480	HPK238 1xHPI-P250W-BU IC 230 50 BK	Inductive parallel compensated	CONV	HPI-P	250 W	1 pc	Base-Up

Order Code	Full Product Name	Compensation circuit	Gear	Lamp family code	Lamp power	Number of light sources	Lamp system description
911401094580	HPK238 1xHPI-P400W-BUS IC 230 50 BK	Inductive parallel compensated	CONV	HPI-P	400 W	1 pc	Base-Up/internal Starter
911401094680	HPK238 1xSON150W IC 230 50 BK	Inductive parallel compensated	CONV	SON	150 W	1 pc	-
911401094980	HPK238 1xHPI-P250W-BU IC 240V-50Hz BK	Inductive parallel compensated	CONV	HPI-P	250 W	1 pc	Base-Up
911401095080	HPK238 1xHPI-P400W-BUS IC 240 50 BK	Inductive parallel compensated	CONV	HPI-P	400 W	1 pc	Base-Up/internal Starter
911401095180	HPK238 1xSON150W IC 240 50 BK	Inductive parallel compensated	CONV	SON	150 W	1 pc	-
911401095280	HPK238 1xSON250W IC 230/240 50 BK	Inductive parallel compensated	CONV	SON	250 W	1 pc	-
911401095380	HPK238 1xSON400W IC 230/240 50 BK	Inductive parallel compensated	CONV	SON	400 W	1 pc	-
911401096280	HPK238 MAX250W-E40 E	-	E	-	-	-	-

Mechanical and Housing

Order Code	Full Product Name	Color	Order Code	Full Product Name	Color
911401092880	HPK238 1xHPI-P250W-BU IC 220 50 BK	Black	911401094480	HPK238 1xHPI-P250W-BU IC 230 50 BK	Black
911401092980	HPK238 1xHPI-P400W-BUS IC 220 50 BK	Black	911401094580	HPK238 1xHPI-P400W-BUS IC 230 50 BK	Black
911401093480	HPK238 1xHPL-N250W IC 220V-60Hz BK	Black	911401094680	HPK238 1xSON150W IC 230 50 BK	Black
911401093580	HPK238 1xHPL-N400W IC 220V-60Hz BK	Black	911401094980	HPK238 1xHPI-P250W-BU IC 240V-50Hz BK	Black
911401093680	HPK238 1xHPI-P250W-BU IC 220 60 BK	Black	911401095080	HPK238 1xHPI-P400W-BUS IC 240 50 BK	Black
911401093880	HPK238 1xSON150W IC 220V-60Hz BK	Black	911401095180	HPK238 1xSON150W IC 240 50 BK	Black
911401093980	HPK238 1xSON250W IC 220V-60Hz BK	Black	911401095280	HPK238 1xSON250W IC 230/240 50 BK	Black
911401094280	HPK238 1xHPL-N250W IC 230 50 BK	Black	911401095380	HPK238 1xSON400W IC 230/240 50 BK	Black
911401094380	HPK238 1xHPL-N400W IC 230 50 BK	Black	911401096280	HPK238 MAX250W-E40 E	-

