



HPK888 Crestbay

Crestbay HPK888

Reliable, effective lighting in any setting is a crucial factor that promotes the senses, productivity, safety and even architecture. Crestbay™ from Philips is precisely designed with this in mind. This highly versatile luminaire delivers outstanding performance in large spaces and in the toughest of environments while assuring quality lighting across a variety of industrial and commercial applications. Moreover, Crestbay™'s innovative SWING-2-BRIGHT™ technology makes maintenance easy, hassle-free and faster than ever before."

Features

- Suitable with a wide range of Philips lamps types; from highpressure mercury and sodium lamps as to compact discharge lamps
- Three types of reflectors: a small aluminium reflector for 70W-250W lamps, a large aluminium reflector for 250W and 400W lamps, and a prismatic acrylic reflector
- All aluminium reflectors have a gloss mirror inner surface with a choice of narrow, medium or wide light beams. Beams can be selected with an adjustable lamp holder
- Each reflector can be fitted with a glass cover to protect against the ingress of dust and moisture
- High-quality components make Crestbay™ able to withstand high ambient temperature
- Easier, safer and faster re-lamping /maintenance via Philips revolutionary SWING-2-BRIGHT™ technology.

Application

- General industries
- Wet and dusty environments
- Public buildings such as exhibition halls, airports, museums
- Discount stores, hyper/ supermarkets, do-it-yourself shops
- High-end fashion outlets

Crestbay HPK888

Versions



Approval and Application

Ingress protection code	IP66
-------------------------	------

Operating and Electrical

Input Voltage	220 V
---------------	-------

General Information

Compensation circuit	Inductive parallel compensated
Optical cover/lens type	-
Gear	CONV
Number of light sources	1 pc

General Information

Order Code	Full Product Name	Protection class IEC	Kombipack	Lamp family code	Lamp power	Optic type	Lamp system description
910401999880	HPK888 1xSON400W IC R-L WH	-	-	SON	400 W	Reflector large	-
910402000180	HPK888 1xHPI-P250W-BU IC R-L WH	-	-	HPI-P	250 W	Reflector large	Base-Up
910402000280	HPK888 1xHPI-P400W-BUS IC R-L WH	-	-	HPI-P	400 W	Reflector large	Base-Up/internal Starter
910402000380	HPK888 1xCDM-T250W IC R-S WH	Safety class I	-	CDM-T	250 W	Reflector small	-
910402000680	HPK888 1xSON400W IC R-L GR	-	-	SON	400 W	Reflector large	-
910402000980	HPK888 1xHPI-P250W-BU IC R-L GR	-	-	HPI-P	250 W	Reflector large	Base-Up
910402001080	HPK888 1xHPI-P400W-BUS IC R-L GR	-	-	HPI-P	400 W	Reflector large	Base-Up/internal Starter

Mechanical and Housing

Order Code	Full Product Name	Color
910401999880	HPK888 1xSON400W IC R-L WH	White
910402000180	HPK888 1xHPI-P250W-BU IC R-L WH	White
910402000280	HPK888 1xHPI-P400W-BUS IC R-L WH	White
910402000380	HPK888 1xCDM-T250W IC R-S WH	White

Order Code	Full Product Name	Color
910402000680	HPK888 1xSON400W IC R-L GR	Gray
910402000980	HPK888 1xHPI-P250W-BU IC R-L GR	Gray
910402001080	HPK888 1xHPI-P400W-BUS IC R-L GR	Gray

