



Product Description

Twistline Alu 2000 hours

Mains-voltage 50 mm diameter reflector lamp with aluminium reflector

Benefits

- Lamp can be connected directly to the mains supply, so no transformers are needed
- UV-Block lamp so no additional front glass or UV filter required
- Twistline dichroic and aluminium versions are the most compact lamps of their kind available

Features

- Quartz burner with Lambda-shape filament optically positioned in a hard-coated aluminium-coated reflector
- Aluminium-coated version (GU10 lamp base) directs most of its heat to the front
- No light goes to the back of the reflector
- Clear front glass protects against touching the burner and against dust/moisture
- Distinct MR16 look
- High and stable light output throughout lifetime
- GU10 bases ensure good retention in the luminaire and easy, 'twist and take out' insertion and replacement
- Built-in double fuses for additional safety at end-of-life

Application


- Typically used for accent lighting in homes
- Also used in accent and general lighting in shops, hotels, restaurants, bars etc.

Twistline Alu 2000 hours

Versions



Dimensional drawing



Product	D (max)	C (max)
Twistline Alu 2000h 50W GU10 240V 40D 1CT/10X5F	50.7 mm	51 mm

