



Spot of crisp white light

Twistline Alu 3000 hours

Mains-voltage long-life halogen burner in glass reflector. Ideal solution for small decorative luminaires, putting your objects in a superior-quality spot light. Aluminum coating prevents heat in the backlight.

Benefits

- Bright, sparkling halogen light to put your objects in the spotlight
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Mains-voltage lamp, no transformer needed
- Lifetime: 3000 hours
- Universal burning position
- Instant start

Application

- Spot accent lighting to create the right ambiance in hotels, restaurants and shops


Twistline Alu 3000 hours

Versions




GU10, MR16

Dimensional drawing



Product	D (max)	C (max)
Twistline Alu 3000h 50W GU10 230V 25D 1CT/10X5F	51 mm	51 mm


Light Distribution Diagrams



Twistline Alu 25D

Twistline Alu 3000 hours

Accent Diagrams



Beam Diagrams

