



# Energy saving alternatives

## Industrial Service

Philips Econ-o-watt® Industrial Service Lamps can directly replace standard life incandescent lamps, offering instant energy savings for many applications.

### Features

- Direct replacement for standard incandescent lamps.
- Energy saving "A" shape lamps.
- Available in a variety of wattages.
- Use as a quick retrofit for 40, 60, 75, 100, and 150W lamps.
- Energy saving- 10%–15% more energy efficient than standard incandescent lamps\*
- Industrial service = 3500 hours rated average life\*\*
- Available in 40, 60, 75, 100, and 150 Watt Frost.
- \*\* Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

### Application


- Ideal for hotels, shops, office buildings and workrooms.

Versions



A21,E26,AL,FR

Dimensional drawing



A21

Product
150A/35RS/BR 120/130V 60PK

