



# Reflector Flood Anti-Vibration

## Reflector BR38 Vibration Service

Philips Specialty Reflector Flood Incandescents provide the perfect light for general lighting in a rough service applications. Designed to withstand vibrations.

### Benefits

- Designed to withstand vibrations in tough service applications.
- Long life.

### Features

- Heavy duty coil to withstand vibrations.
- Rated average life of 5000 hours+
- Available in 150 watts.
- +Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

### Application

- Ideal for rough service applications


## Reflector BR38 Vibration Service

### Versions



E26, BR38, Clear

### Dimensional drawing



#### Product

150BR38/5FL 12/1 PK

