



# Mini Reflector

## Mini Reflector

Philips Family of Mini Reflector bulbs provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications.

### Features

- Compact spot light
- Available in: R14 Intermediate: 25 Watt; R14 and R16 Medium: 40 watt.

### Application

- Ideal for cabinets, display lighting, and small recessed track fixtures.

### Versions




E17, R14, Reflector



E17, R14, Frosted

# Mini Reflector

## Dimensional drawing



Product	D	C (max)
BC40R14N 120V 6/1 TP	1.75 in	2.625 in
BC-40R14/N	1.75 in	2.625 in

Operating and electrical	
Voltage (Nom)	120 V
Power (Nom)	40 W
General information	
Cap-Base	E17
Rated Lifetime (Hours)	1500 h
Light technical	
Beam Description	Flood
Mechanical and housing	
Bulb Shape	R-14

## Operating and electrical

Order Code	Full Product Name	Lamp Wattage Rated@120V
925173136304	BC40R14N 120V 6/1 TP	40 W

Order Code	Full Product Name	Lamp Wattage Rated@120V
925271036302	BC-40R14/N	-

## General information

Order Code	Full Product Name	Operating Position
925173136304	BC40R14N 120V 6/1 TP	UNIVERSAL

Order Code	Full Product Name	Operating Position
925271036302	BC-40R14/N	S90

## Mechanical and housing

Order Code	Full Product Name	Bulb Finish
925173136304	BC40R14N 120V 6/1 TP	Reflector

Order Code	Full Product Name	Bulb Finish
925271036302	BC-40R14/N	Frosted

## Mini Reflector

