



# Incandescent Reflector Par 36

## Reflector PAR36

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications.

### Features

- Offers a dirt-free, maintenance-free light system.
- Features a filament shielding for reduced light source glare.
- Reduced heat build up in the fixture.
- Available in 50 watts Compact Wide Flood, Compact Narrow Flood MP versions.

### Application

- Ideal for down lights, track lighting, up lighting and general illumination in home, retail and hospitality applications.


### Versions



Screw Terminal, PAR36

## Reflector PAR36

### Dimensional drawing



#### Product

50PAR36/WFL 12V 12PK

