



Lamp:

Standard Candle B35 frosted

Flame-shaped bulb with clear or inside-frosted glass and vacuum- or gas-filled bulb

Benefits

- Graceful lamps that enhance the elegance of classical chandeliers, candelabras, wall brackets etc.
- Set the scene for cosiness and comfort, used with or without lampshades

Features

- Clear lamps:
 - slender, crystal-clear lamps designed for sparkling highlights
 - creates a classic sparkling atmosphere
- Frosted lamps:
 - slender, frosted lamps
 - creates a low-glare atmosphere
- Universal burning position except for some 60W types which must be operated vertically, base-down (tolerance 90°)

Application


- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches

Standard Candle B35 frosted

Versions



Dimensional drawing



Product	D	C (max)
Stan 25W E14 220-240V B35 FR 1CT/5X10F	35 mm	100 mm
Stan 40W E14 220-240V B35 FR 1CT/5X10F	35 mm	100 mm

General Information

Cap-Base	E14
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL

Light Technical

Color rendering index (CRI)	100
-----------------------------	-----

Operating and Electrical

Voltage (Nom)	220-240 V
---------------	-----------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	B35

Light Technical

Order Code	Full Product Name	Luminous Flux
921486643301	Stan 25W E14 220-240V B35 FR 1CT/5X10F	210 lm
921491643301	Stan 40W E14 220-240V B35 FR 1CT/5X10F	410 lm

Operating and Electrical

Order Code	Full Product Name	Power Consumption
921486643301	Stan 25W E14 220-240V B35 FR 1CT/5X10F	25 W

Order Code	Full Product Name	Power Consumption
921491643301	Stan 40W E14 220-240V B35 FR 1CT/5X10F	40 W

Standard Candle B35 frosted

