

Product Description

Deco Candle Twisted BW-shape clear

Twisted, flame-shaped bulb with clear glass and vacuum- or gas-filled bulb with B- or E-base

Benefits

- At their best in decorative glass chandeliers and wall lamps with clear or textured glass bowls
- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Clear lamps designed for sparkling highlights

Application

- Home use in living and dining rooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Ballrooms
- Shops and boutiques
- Churches


Deco Candle Twisted BW-shape clear

Versions



E14, BW35, CL

Dimensional drawing



Product	D	C (max)
Deco 40W E14 230V BW35 CL 1CT/4X5F	35 mm	100 mm
Deco 60W E14 230V BW35 CL 1CT/4X5F	35 mm	100 mm

Approval and Application

Energy Efficiency Label (EEL) E

Controls and Dimming

Dimmable Yes

Operating and Electrical

Voltage (Nom) 230 V

General Information

Cap-Base E14

Nominal Lifetime (Nom) 1000 h

Rated Lifetime (Hours) 1000 h

Light Technical

Color Rendering Index (Nom) 100

Mechanical and Housing

Bulb Finish Clear

Bulb Shape BW35

Operating and Electrical

Order Code	Full Product Name	Power (Rated) (Nom)
921494144216	Deco 40W E14 230V BW35 CL 1CT/4X5F	40 W
921502044219	Deco 60W E14 230V BW35 CL 1CT/4X5F	60 W

General Information

Deco Candle Twisted BW-shape clear

Order Code	Full Product Name	Operating Position
921494144216	Deco 40W E14 230V BW35 CL 1CT/4X5F	UNIVERSAL

Order Code	Full Product Name	Operating Position
921502044219	Deco 60W E14 230V BW35 CL 1CT/4X5F	S90

Light Technical

Order Code	Full Product Name	Luminous Flux (Nom)
921494144216	Deco 40W E14 230V BW35 CL 1CT/4X5F	400 lm

Order Code	Full Product Name	Luminous Flux (Nom)
921502044219	Deco 60W E14 230V BW35 CL 1CT/4X5F	655 lm

