



Product Description

Standard Extra Low Voltage A60

Clear lamp (A-bulb) for operation on voltages of 12, 24, 42 and 50 V

Benefits

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

Features

- Types till 42 V are safer in combination with a mains power supply transformer

Application

- Rural and isolated areas where mains power supplies are not available
- Emergency lighting installations

Versions



E27 A 60mm Clear

Standard Extra Low Voltage A60

Dimensional drawing

Product	D (max)	C (max)
Standard ELV 60W E27/BRC 24V A60 CL 1CT/20	2-3/8 in	4-1/4 in

