



## Lampe :

### Standard Très bas voltage

Lampe claire pour tensions 24V

#### Avantages

- Provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications
- Gas-filled lamp has a clear glass are ideally suited for remote, isolated areas where energy has to be supplied by private generating plants, batteries or other low-voltage sources
- Used when brilliance is an advantage

#### Fonctions

- Toutes positions de fonctionnement

#### Application

- Zones rurales et isolées ne disposant pas de la tension d'alimentation secteur
- Installations d'éclairage d'urgence

#### Versions



## Standard Très bas voltage

### Schéma dimensionnel

| Product                                 | D (max) | C (max)  |
|---|---------|----------|
| Standard ELV 40W E27/BRC 24V A60 CL 1CT | 60 mm   | 107,5 mm |

