



Instant heat exactly where and when needed

InfraRed Industrial Heat Incandescent

The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, people, but also food. These benefits have made farmers, consumers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Benefits

- 30% extra energy saving with PAR thanks to its unique reflector system
- Simple and safe heat source with no risk of broken glass
- 90% of energy is transmitted as infrared heat.

Features

- Robust and sturdy hard glass construction of entire range of infrared reflectors.
- Reflector shape allows concentrated heat to be applied to where it is needed.
- The design of PAR38 incorporates a completely sealed reflector and therefore high efficiency.
- More hassle free and handy replacement period thanks to long durability of infrared lamps
- Red-coloured lamps to reduce visual light emission and glare.

InfraRed Industrial Heat Incandescent

Application


- Agricultural: breeding and rearing of pigs, poultry, calves, foals, dogs etc. as well as in veterinary clinics, zoos, pet shops.
- General radiant heating, e.g. hot food displays, cooker hoods, bathrooms, space heating etc.
- Industrial heating, e.g. drying, baking, carbonising, melting etc.

Versions



LPPR IRSG E27 R125 Clear

Dimensional drawing



Product	D	C (max)
BR125 IR 250W E27 230-250V CL 1CT/10	125 mm	173 mm
BR125 IR 250W E27 230-250V Red 1CT/10	125 mm	173 mm

General Information	
Cap-Base	E27
Rated Lifetime (Hours)	5,000 hour(s)
Nominal lifetime	5,000 hour(s)
Operating and Electrical	
Voltage (Nom)	230-250 V
Power Consumption	250 W
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Hard Glass
Bulb Shape	BR125

General Information

Order Code	Full Product Name	Operating Position
923212043801	BR125 IR 250W E27 230-250V Red 1CT/10	H45
923212143801	BR125 IR 250W E27 230-250V CL 1CT/10	UNIVERSAL

InfraRed Industrial Heat Incandescent

Mechanical and Housing

Order Code	Full Product Name	Bulb Finish
923212043801	BR125 IR 250W E27 230-250V Red 1CT/10	Red

Order Code	Full Product Name	Bulb Finish
923212143801	BR125 IR 250W E27 230-250V CL 1CT/10	Clear

