



# Product Description

## Standard Lustre P45 clear

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

### Benefits

- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

### Features

- Small, crystal-clear lamps designed for sparkling highlights
- At their best in decorative small luminaires such as table models and wall brackets with clear glass bowls
- Creates a sparkling atmosphere

### Application


- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

# Standard Lustre P45 clear

## Versions



## Dimensional drawing



Product	D	C (max)
Standard 40W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

