



Product Description

Standard Lustre P45 clear

Spherical vacuum- or gas-filled incandescent lamps with a clear glass bulb and E- or B-base

Benefits

- Brilliant, visible filament adds small points of brightness for an enriched lighting effect

Features

- Small, crystal-clear lamps designed for sparkling highlights
- At their best in decorative small luminaires such as table models and wall brackets with clear glass bowls
- Creates a sparkling atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas

Standard Lustre P45 clear

Versions






LPPR ITUBAPE 0001



LPPR ILUSBSTD B22 P45 CL

Dimensional drawing




Product	D	C (max)
Stan 40W E27 127V P45 CL U OV 1CT/5X10F	45 mm	73 mm

Product	D	C (max)
230V 15W GLS CLEAR BAYONET CAP	45 mm	71.5 mm

Product	D	C (max)
Stan 40W E14 230V P45 CL 1CT/10X10F	45 mm	78 mm

Standard Lustre P45 clear

Dimensional drawing



Product	D	C (max)
Stan 15W E27 220-240V P45 CL 1CT/50X10F	45 mm	73 mm
Stan 25W E27 220-240V P45 CL 1CT/5X10F	45 mm	73 mm
Stan 40W E27 220-240V P45 CL 1CT/5X10F	45 mm	73 mm
Stan 40W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm
Stan 60W E27 230V P45 CL 1CT/10X10F	45 mm	73 mm

General Information	
Nominal lifetime	1,000 hour(s)
Light Technical	
Color rendering index (CRI)	100
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Operating Position
923268735892	Stan 40W E27 127V P45 CL U OV 1CT/5X10F	E27	-	UNIVERSAL
921400544299	230V 15W GLS CLEAR BAYONET CAP	B22	-	UNIVERSAL
921402443348	Stan 15W E27 220-240V P45 CL 1CT/50X10F	E27	-	UNIVERSAL
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	E27	1,000 hour(s)	UNIVERSAL

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)	Operating Position
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	E27	1,000 hour(s)	UNIVERSAL
926000005857	Stan 60W E27 230V P45 CL 1CT/10X10F	E27	1,000 hour(s)	S90
926000006412	Stan 40W E27 230V P45 CL 1CT/10X10F	E27	1,000 hour(s)	UNIVERSAL
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	E14	1,000 hour(s)	UNIVERSAL

Light Technical

Order Code	Full Product Name	Luminous Flux
923268735892	Stan 40W E27 127V P45 CL U OV 1CT/5X10F	455 lm
921400544299	230V 15W GLS CLEAR BAYONET CAP	110 lm
921402443348	Stan 15W E27 220-240V P45 CL 1CT/50X10F	115 lm
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	200 lm

Order Code	Full Product Name	Luminous Flux
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	385 lm
926000005857	Stan 60W E27 230V P45 CL 1CT/10X10F	640 lm
926000006412	Stan 40W E27 230V P45 CL 1CT/10X10F	390 lm
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	405 lm

Operating and Electrical

Standard Lustre P45 clear

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Starting Time (Nom)
923268735892	Stan 40W E27 127V P45 CL U OV 1CT/5X10F	127 V	40 W	0.0 s
921400544299	230V 15W GLS CLEAR BAYONET CAP	230 V	15 W	-
921402443348	Stan 15W E27 220-240V P45 CL 1CT/50X10F	220-240 V	15 W	-
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	220-240 V	25 W	-

Order Code	Full Product Name	Voltage (Nom)	Power Consumption	Starting Time (Nom)
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	220-240 V	40 W	-
926000005857	Stan 60W E27 230V P45 CL 1CT/10X10F	230 V	60 W	-
926000006412	Stan 40W E27 230V P45 CL 1CT/10X10F	230 V	40 W	-
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	230 V	40 W	-

Controls and Dimming

Order Code	Full Product Name	Dimmable
923268735892	Stan 40W E27 127V P45 CL U OV 1CT/5X10F	-
921400544299	230V 15W GLS CLEAR BAYONET CAP	Yes
921402443348	Stan 15W E27 220-240V P45 CL 1CT/50X10F	Yes
921411543301	Stan 25W E27 220-240V P45 CL 1CT/5X10F	Yes

Order Code	Full Product Name	Dimmable
921421543301	Stan 40W E27 220-240V P45 CL 1CT/5X10F	Yes
926000005857	Stan 60W E27 230V P45 CL 1CT/10X10F	Yes
926000006412	Stan 40W E27 230V P45 CL 1CT/10X10F	Yes
926000006511	Stan 40W E14 230V P45 CL 1CT/10X10F	Yes

