



Product Description

Standard Lustre P45 frosted

Spherical vacuum- or gas-filled incandescent lamps with white or inside-frosted glass bulb and E- or B-base

Benefits

- Softly diffused light sets the scene for cosiness and comfort, and meets both aesthetic and functional requirements

Features

- Lamps with reduced size and neat shape
- Extremely popular for use around mirrors or in chandeliers, candelabras, floor lamps and wall brackets, fitted with small, decorative shades
- Creates a pleasant low glare atmosphere

Application

- Home use in living and dining rooms, bedrooms, halls and studies
- Hotel lounges, restaurants, bedrooms, halls, conference rooms and foyers
- Clubs and social areas
- Shops, boutiques and department stores
- Other similar areas



Standard Lustre P45 frosted

Versions



LPPR ILUSESTD E27 P45 CL

Dimensional drawing



Product	D	C (max)
Stan 25W E14 220-240V P45 FR 1CT/5X10F	45 mm	78 mm
Stan 40W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm
Stan 60W E14 230V P45 FR 1CT/10X10F	45 mm	78 mm

Product	D	C (max)
Stan 25W E27 220-240V P45 FR 1CT/5X10F	45 mm	73 mm
Stan 40W E27 220-240V P45 FR 1CT/5X10F	45 mm	73 mm
Stan 40W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm
Stan 60W E27 230V P45 FR 1CT/10X10F	45 mm	73 mm

Standard Lustre P45 frosted

General Information	
Rated Lifetime (Hours)	1,000 hour(s)
Nominal lifetime	1,000 hour(s)
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45

General Information

Order Code	Full Product Name	Cap-Base	Operating Position
921411143301	Stan 25W E14 220-240V P45 FR 1CT/5X10F	E14	UNIVERSAL
921411643301	Stan 25W E27 220-240V P45 FR 1CT/5X10F	E27	UNIVERSAL
921421643301	Stan 40W E27 220-240V P45 FR 1CT/5X10F	E27	UNIVERSAL

Order Code	Full Product Name	Cap-Base	Operating Position
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	E27	S90
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	E14	UNIVERSAL
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	E27	UNIVERSAL

Light Technical

Order Code	Full Product Name	Luminous Flux
921411143301	Stan 25W E14 220-240V P45 FR 1CT/5X10F	210 lm
921411643301	Stan 25W E27 220-240V P45 FR 1CT/5X10F	200 lm
921421643301	Stan 40W E27 220-240V P45 FR 1CT/5X10F	385 lm
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	640 lm

Order Code	Full Product Name	Luminous Flux
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	650 lm
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	405 lm
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	390 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
921411143301	Stan 25W E14 220-240V P45 FR 1CT/5X10F	220-240 V	25 W
921411643301	Stan 25W E27 220-240V P45 FR 1CT/5X10F	220-240 V	25 W
921421643301	Stan 40W E27 220-240V P45 FR 1CT/5X10F	220-240 V	40 W
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	230 V	60 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	230 V	60 W
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	230 V	40 W
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	230 V	40 W

Approval and Application

Order Code	Full Product Name	Energy Consumption kWh/1000 h
921411143301	Stan 25W E14 220-240V P45 FR 1CT/5X10F	-
921411643301	Stan 25W E27 220-240V P45 FR 1CT/5X10F	-

Order Code	Full Product Name	Energy Consumption kWh/1000 h
921421643301	Stan 40W E27 220-240V P45 FR 1CT/5X10F	-
926000003568	Stan 60W E27 230V P45 FR 1CT/10X10F	60 kWh

Standard Lustre P45 frosted

Order Code	Full Product Name	Energy Consumption kWh/1000 h
926000003857	Stan 60W E14 230V P45 FR 1CT/10X10F	60 kWh
926000007010	Stan 40W E14 230V P45 FR 1CT/10X10F	-

Order Code	Full Product Name	Energy Consumption kWh/1000 h
926000007412	Stan 40W E27 230V P45 FR 1CT/10X10F	-

