



Sumo electronic ballast for TL-D/TL5 lamps

Sumo Electronic ballast for TL5/TL-D lamps (India)

Compact, lightweight, high-frequency electronic ballasts for TL-D/TL5 fluorescent lamps

Benefits

- More than 25% reduction in energy consumption compared with conventional electromagnetic ballasts at equal luminous flux
- No blackening of walls

Features

- Flicker-free instant start
- Minimum ignition voltage of 90 V
- Footprint (fixing holes) matches conventional electromagnetic potted ballast

Application

- Home
- Retail
- Areas with acute low-voltage problems


Sumo Electronic ballast for TL5/TL-D lamps (India)

Versions



Sumo ultra 136

Dimensional drawing



Product	D1	C1	A1	A2	B1
Sumo ultra 136	4.0 mm	27.0 mm	136.0 mm	130.0 mm	40.0 mm

