



Product Description

PAR38 Colours

Coloured pressed-glass 121 mm diameter reflector lamp

Benefits

- Gives striking decorative effects, both indoors and outdoors
- 20% lower power consumption compared with conventional coloured PAR lamps

Features

- Weatherproof coloured coating on the refractor face in a choice of colours
- Flood beam width

Application

- Parks, public and private gardens
- Festive illumination
- Restaurants, bars, dance halls, discotheques
- Show-window displays, fountains and 'Son et Lumi' spectacles
- Can be installed outdoors without any protection, provided they are used in a watertight lampholder
- For outdoor use, a heat-resistant rubber ring must be fitted between the lamp and the lampholder


PAR38 Colours

Versions



PAR38, E27, Green

Dimensional drawing



| Product | D (max) | C (max) |
|--------------------------------------|---------|---------|
| PAR38 Colours 80W E27 230V GR 1CT/12 | 123 mm | 137 mm |

