



Product Description

Reinforced Construction A-shape

Reinforced Incandescent lamp with A-shape for heavy duty applications

Benefits

- Longer lifetime (>2000 hrs) when used in heavy duty applications as compared to standard incandescent lamps

Features

- Reinforced construction lamp with exceptionally strong filament to withstand mechanical shocks and vibrations

Application

- Where longer lifetime is required in combination with shock-resistant needs
- Hand-held inspection lights
- Task lights in maintenance and automotive service shops


Versions



E27, A60/A65, Frosted

Reinforced Construction A-shape

Dimensional drawing



Product	D (max)	C (max)
Reinforced Construction 100W E27 230V A60 FR 1CT/20	60 mm	107.5 mm

