



## Product Description

### Reflector Colours diam 50/63/80 mm

Externally lacquered reflector lamps in various colours for striking indoor lighting effects

#### Benefits

- 25% more light in the centre of the beam (NR50 and NR63 versions) than standard coloured reflector lamps
- NR50 and NR63 versions are small lamps producing low illuminance levels for subdued lighting

#### Features

- More concentrated beam with less stray light, providing a high degree of visual comfort
- Significantly improved beam light distribution, with no black spots
- Modern appearance with distinctive flatter-top shape and recessed neck
- Produced with cadmium-free lacquer

#### Application

- Homes children's bedrooms and in-house bars
- Social areas, bars, night clubs, dance halls, theatres
- Show windows


Reflector Colours diam 50/63/80 mm

Versions



E14, NR50, Red

Dimensional drawing



Product	D (max)	C (max)
Reflector Colours 40W E14 230V NR50 CL-RE 1CT/15	50 mm	87 mm

