



## Product Description

### Reflector diam 80/90/95/125 mm

Normal incandescent lamps with an internal ring-shaped parabolic aluminium mirror behind the filament

#### Benefits

- Beam spread and luminous intensity make these lamps especially suitable wherever space is limited and in small luminaires

#### Features

- Blown glass bulb with frosted front
- Wide choice of diameters and wattages
- Lamp is designed to achieve brilliant indoor lighting effects

#### Application

- Homes, shops, shop windows and displays, restaurants, hotels, exhibitions, bars and night clubs


#### Versions




E27, NR80

Reflector diam 80/90/95/125 mm


Dimensional drawing




Product	D
Reflector 60W E27 230V NR80 25D 1CT/30	80 mm



Accent Diagrams



Beam Diagrams



LDBE\_IREFESP\_60W\_NR80\_25D-Beam diagram

Reflector diam 80/90/95/125 mm

