



Product Description

Standard A-shape clear

Conventional pear-shaped incandescent lamps

Benefits

- Brilliant, visible filament adds friendly points of brightness for an enriched lighting effect

Features

- Vacuum-filled (15W) or gas-filled (25W and above)

Application



- Clear lamps are ideal for indirect lighting in closed luminaires, and where brilliance and sparkling effects are more important than reduction of glare

Versions



Standard A-shape clear

Dimensional drawing



Product	D	C (max)
Stan 100W B22 220-240V A55 CL 1CT/5X10F	55 mm	95.5 mm

Product	D (max)	D	C (max)
Stan 100W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 100W E27 220V A55 CL U 1CT/10X10F	56 mm	55 mm	97 mm
Stan 100W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 100W E27 240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm
Stan 40W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 40W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 60W E27 220-240V A55 CL 1CT/5X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 60W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 60W E27 240V A55 CL 1CT/10X10F	56 mm	55 mm	97 mm
Stan 75W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm
Stan 75W E27 230V A55 CL 1CT/12X10F	56 mm	55 mm	97 mm

General Information	
Nominal lifetime	1,000 hour(s)
Operating Position	UNIVERSAL
Light Technical	
Color rendering index (CRI)	100
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A55

General Information

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
920053843301	Stan 40W E27 220-240V A55 CL 1CT/5X10F	E27	-
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	E27	-
920054645597	Stan 60W E27 240V A55 CL 1CT/10X10F	E27	-
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	E27	-

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	E27	-
926000000885	Stan 40W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)
926000004004	Stan 75W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)
926000004009	Stan 100W E27 240V A55 CL 1CT/10X10F	E27	-
926000004012	Stan 100W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)

Standard A-shape clear

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
926000004013	Stan 75W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)
926000010339	Stan 60W E27 230V A55 CL 1CT/12X10F	E27	1,000 hour(s)

Order Code	Full Product Name	Cap-Base	Rated Lifetime (Hours)
920056043301	Stan 100W B22 220-240V A55 CL 1CT/5X10F	B22	-

Light Technical

Order Code	Full Product Name	Luminous Flux
920053843301	Stan 40W E27 220-240V A55 CL 1CT/5X10F	415 lm
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	710 lm
920054645597	Stan 60W E27 240V A55 CL 1CT/10X10F	700 lm
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	1,340 lm
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	1,340 lm
926000000885	Stan 40W E27 230V A55 CL 1CT/12X10F	415 lm
926000004004	Stan 75W E27 230V A55 CL 1CT/12X10F	930 lm

Order Code	Full Product Name	Luminous Flux
926000004009	Stan 100W E27 240V A55 CL 1CT/10X10F	1,320 lm
926000004012	Stan 100W E27 230V A55 CL 1CT/12X10F	1,340 lm
926000004013	Stan 75W E27 230V A55 CL 1CT/12X10F	930 lm
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	710 lm
926000010339	Stan 60W E27 230V A55 CL 1CT/12X10F	710 lm
920056043301	Stan 100W B22 220-240V A55 CL 1CT/5X10F	1,340 lm

Operating and Electrical

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
920053843301	Stan 40W E27 220-240V A55 CL 1CT/5X10F	220-240 V	40 W
920054643302	Stan 60W E27 220-240V A55 CL 1CT/5X10F	220-240 V	60 W
920054645597	Stan 60W E27 240V A55 CL 1CT/10X10F	240 V	60 W
920056542905	Stan 100W E27 220V A55 CL U 1CT/10X10F	220 V	100 W
920056543301	Stan 100W E27 220-240V A55 CL 1CT/5X10F	220-240 V	100 W
926000000885	Stan 40W E27 230V A55 CL 1CT/12X10F	230 V	40 W
926000004004	Stan 75W E27 230V A55 CL 1CT/12X10F	230 V	75 W

Order Code	Full Product Name	Voltage (Nom)	Power Consumption
926000004009	Stan 100W E27 240V A55 CL 1CT/10X10F	240 V	100 W
926000004012	Stan 100W E27 230V A55 CL 1CT/12X10F	230 V	100 W
926000004013	Stan 75W E27 230V A55 CL 1CT/12X10F	230 V	75 W
926000006627	Stan 60W E27 230V A55 CL 1CT/12X10F	230 V	60 W
926000010339	Stan 60W E27 230V A55 CL 1CT/12X10F	230 V	60 W
920056043301	Stan 100W B22 220-240V A55 CL 1CT/5X10F	220-240 V	100 W

