



Product Description

Deco Tubular

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

Benefits

- Give brilliant and decorative lighting effects
- Ideal for creating a comfortable and relaxing ambience

Features

- Internal coating cannot chip, fade, become scratched or weathered

Application

- General lighting: switchboards, cupboards, piano and painting lighting
- Clear lamps:
- industrial/professional lighting: sign boards, elevator sign systems, fair and festive lighting
- Lamps with inside-frosted bulb:
- ideal for a wide range of domestic and industrial applications

Versions



Deco Tubular

Dimensional drawing



Product	D	C (max)
15W E14 220-240V T25 CL 2BC/5	25 mm	54 mm

