



# Product Description

## Deco Tubular

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base

### Benefits

- Give brilliant and decorative lighting effects
- Ideal for creating a comfortable and relaxing ambience

### Features

- Internal coating cannot chip, fade, become scratched or weathered

### Application


- General lighting: switchboards, cupboards, piano and painting lighting
- Clear lamps:
- industrial/professional lighting: sign boards, elevator sign systems, fair and festive lighting
- Lamps with inside-frosted bulb:
- ideal for a wide range of domestic and industrial applications

### Versions



Deco Tubular

Dimensional drawing



Product	D	C (max)
40W E14 240V T25L CL CH 1CT/10x10F	25 mm	81 mm

