



Product Description

Appliance Oven Tubular

Tubular vacuum lamps with clear glass (T-bulb)

Benefits

- Reliable operation when used in special lampholders at high oven temperatures (up to 300°C)

Features

- Coiled-coil filament
- Manufactured with heat-resistant solder, getter and lamp-base cement

Application

- Electrical and standard ovens, rotisseries and similar places subject to high operating temperatures
- Available for specific oven luminaires fitted in different positions such as downlighter, side-light and backlight

Versions



Appliance Oven Tubular

Dimensional drawing

| Product | D (max) | C (max) |
|--|---------|---------|
| Appliance 25W E14 230-240V T25 CL OV 1CT | 25 mm | 57 mm |

