



Product Description

Appliance Refrigerator Tubular

Tubular lamp with clear glass bulb

Benefits

- Long useful life in refrigerators and freezers
- Long useful life in refrigerators and freezers

Features

- Reinforced filament
- Reinforced filament
- T-CLICK design with integrated lampholder reduces integral costs of refrigerator lighting
- T-CLICK design with integrated lampholder reduces integral costs of refrigerator lighting

Application

- Refrigerators and freezers
- Refrigerators and freezers

Versions



LPPR ITUBAPE 0001

Appliance Refrigerator Tubular

Dimensional drawing

Product	D (max)	C (max)
Appl 15W E14 230-240V T25 CL RF 2BL/10	25 mm	57 mm

