



# Smart Modular Downlight LBX300C – Cool... light your environment in a safe and smart way

## Basic Modular LBX300

Our Smart Modular Downlight is an affordable, reliable and flexible solution designed to deliver both general and accent lighting in retail environments. Driven by electronic and electromagnetic gear, the trendy Smart Modular Downlight combines an attractive visual appearance with ease of installation and maintenance. A robust housing and high-quality components ensure the product's long lifetime.

### Benefits

- Durable and safe
- Flexible and convenient
- Trendy and professional design

### Features

- IEC60598 and CCC-compliant
- Electronic and electromagnetic ballast
- Robust housing
- High-quality lamp holders and connectors
- Emergency-lighting version available

### Application

- Retail

### Specifications

## Basic Modular LBX300

<b>Type</b>	LBX300 (Halogen Accentline lamp version)
	LBX301 (Halogen Capsuleline lamp version)
	CBX301 (HID CDM-T / Halogen Capsuleline lamps version)
<b>Light source</b>	Halogen:
<b>Mechanical and Housing</b>	- 1, 2 or 3 x Capsuleline / GY6.35 / 50 W
	- 1, 2, 3 or 4 x Accentline / GU5.3 / 50 W
	HID:
	- 1 x MASTERColour CDM-T / G12 / 70 W
<b>Lamp included</b>	No
<b>Lamp position</b>	Vertical

<b>Light distribution</b>	Direct
<b>Ballast</b>	Electronic, High Frequency 220-240 V / 50-60 Hz:
	- Electronic
<b>Transformer</b>	Electronic for halogen lamp version, 220-240 V
<b>Optic</b>	Wide beam (for CDM-T lamp version only)
	Narrow beam (for Capsuleline lamp version only)
<b>Connection</b>	SCREW connector
<b>Material</b>	Housing: anodised aluminum with matt surface
<b>Color</b>	Frame: white (WH) and grey (GR)
<b>Installation</b>	Fixation by means of spring fasteners

### Versions



Basic Modular LBX300



Basic Modular LBX300



Basic Modular LBX300

#### Operating and Electrical

Maximum lamp power	MAX50
--------------------	-------

#### General Information

Cap-Base	GU5.3
Compensation circuit	-
Gear	-
Number of light sources 2	-

### General Information

Order Code	Full Product Name	Number of light sources
910403630425	LBX300 1xMAX50W/12V-GU5.3 WH	1

Order Code	Full Product Name	Number of light sources
910403630428	LBX300 2xMAX50W/12V-GU5.3 GR	2

