



Accessories – completing your Luminaire Based System

Luminaire Based Accessoires

Luminaire Based Accessories cover a generic range of products which can be used to extend functionality and/or simplify the design-in of our luminaire based systems.

Benefits

- Luminaire based accessories offer the possibility to extend the ActiLume family
- Accessories are clips, covers, rings and extension sensors
- Clips will ease the installation of sensors by making it possible to clip them onto the lamp
- Covers and rings are to obtain the same outer dimensions across the ActiLume family sensors and extension sensors
- Ease of installation

Features

- Philips ActiLume systems are DALI- or 1-10V based lighting control system designed for maximum comfort and energy savings of up to 75% (in fully automatic mode and when used in combination with Philips HF-Regulator Touch and DALI or 1-10V ballasts)

Application

- Luminaire based accessories are designed for all ActiLume systems used in office applications, from open-plan to cell offices, lobbies or toilets, and from corridors to small meeting rooms


Luminaire Based Accessoires

Versions



LRM8140/00 ActiLume G2 RF Mov Sensor

Dimensional drawing



Product

LRM8119/00 Lum Based Ext Sensor 100cm

Product details



LRM8119/00 Lum Based Ext
Sensor with LCA8004/00 COVER



LRM8119/00 Lum Based Ext
Sensor with LCA8004/00 COVER



LRM8119/00 Lum Based Ext
Sensor with LCA8004/00 COVER



LRM8119/00 Lum Based Ext
Sensor with LCA8004/00 COVER

Luminaire Based Accessoires

Product details



LRM8140/00 ActiLume G2 RF Mov
Sensor - Front

