



# Chronosense - the flexible stand-alone dimming solution

## Chronosense

Luminaire based, stand-alone controller for magnetic ballasts up to 600 W. The design of Chronosense is optimized for mounting in a luminaire or gear tray. Step-dim schedule is created using 5 dip switches, dim schedule is flexible between 4 and 9 hours around the midpoint of the night.

### Benefits

- Energy savings of up to 30%
- Stand-alone, no commissioning, no operational costs
- Reduced light nuisance

### Features

- Simple dip switch settings to set/reset the dim period
- Small size with smart connectors for easy mounting
- Midpoint of the night calculation guarantees maximum savings

### Application

- Roads, streets Residential and area lighting, including parking lots, ports, train stations and industrial complexes

## Versions

