

PHILIPS

Lighting



Fugato Adjustable

Fugato Adjustable

Fugato 通用系列由固定式和可調整式嵌燈組成，為照明設計打造更遼闊的創意空間。不僅如此，Fugato 可調式燈具 提供多種懸掛或內部 / 外部全幅調整型號。燈具使用靈活，光學鏡片選擇多樣 (某些型號使用創新雙層鏡片)，照明設計更能自由揮灑。此外，此款燈具的可調整型和固定型產品，尺寸、外觀完全相同，確保燈具組外觀協調一致。Fugato 嵌燈具 5 種不同的尺寸 (95、125、175、225 和 275 毫米開孔)。固定式 Fugato 嵌燈可安裝 CFL 省電燈泡、氣體放電式燈和鹵素燈；可調式與萬向懸掛式則限氣體放電式燈和鹵素燈。光學創新設計 突破性「雙光學片設計」，上方為金屬反光片，下方為金屬聚合鏡片。與單片聚合透光片相比，雙光學片優點眾多，例如散熱性更佳等，還能與功能性和結構性配件直接整合，並可選擇高光澤度、霧面或白色塗佈。舒適的辦公照明 Fugato 嵌燈無論流明輸出、光電效率和眩光指數均力求完美，共有 5 種尺寸，適合替換現有大型或方形辦公室燈具。採用頂級光學元件，光線輸出優異，有效遮擋眩光 (符合 CIE EN12464-1 規範)，呈現高效照明品質。另有先進的電子控制型，節省大量電力。多功能照明 Fugato 結合絕佳燈光輸出、照明效能以及防眩光等級，絕對是大型與方形燈具的最佳替換選擇。多樣化的選購配件、光學元件塗佈及整合式照明控制，營造出更舒適的照明環境。

特点

- 採用頂級光學元件，光線輸出優異，有效遮擋眩光，呈現高效照明品質。
- 懸掛式及可調式 讓您自由調整，配合不同的低天花板照明設計。
- 燈頭指向：
- Micro Cardanic (袖珍懸掛型)：垂直 40°
- Mini Cardanic (迷你懸掛型)：水平 357°，垂直 40°
- Mini Adjustable (迷你可調型)：水平 357°，垂直 45°
- Compact Cardanic (微懸掛型)：水平 357°，垂直 40°
- Compact Adjustable (微型可調)：水平 357°，垂直 80° (外部) 和 40° (內部)。

应用

- 室內公共空間
- 辦公室
- 飯店
- 店面
- 環境

Fugato Adjustable

Versions



Approval and Application

防水防塵規範 (IP) IP20

General Information

國家版本 NO
裝置 EB
燈具系列代碼 CDM-TC
光源數 1

Mechanical and Housing

色彩 WH

General Information

Order Code	Full Product Name	燈具功率	光學裝置類型
911400807680	MBS254 C 1xCDM-TC70W EB 12 WH	70 W	12
911400807780	MBS254 C 1xCDM-TC35W EB 24 WH	35 W	24
911400807880	MBS254 C 1xCDM-TC70W EB 24 WH	70 W	24

Order Code	Full Product Name	燈具功率	光學裝置類型
911400808480	MBS252 C 1xCDM-TC35W EB 24 WH	35 W	24
911400808580	MBS252 C 1xCDM-TC70W EB 24 WH	70 W	24

