



Fugato Fixed MBS250/260, FBS261/270/271/280

Fugato Fixed

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Features

- Optical variation is offered by means of Fugato's dual optic concept: top reflector determining the beam angle and lower optic creating a comfortable lighting effect
- In the Fugato concept there is a seamless transition from the lower optic to the rim, rendering a clean visual articulation of the luminaire for ceiling installation

Application

- Fashion stores
- Chain stores
- Shopping malls
- Departmental stores
- Showrooms
- Offices

Fugato Fixed

Versions



Approval and Application	
Ingress protection code	IP20
General Information	
Gear	EB
Lamp family code	CDM-TC
Number of light sources	1
Optic type	36
Mechanical and Housing	
Colour	White

General Information

Order Code	Full Product Name	Lamp power
00808980	MBS250 C 1xCDM-TC35W EB 36 WH	35 W

Order Code	Full Product Name	Lamp power
00809080	MBS250 C 1xCDM-TC70W EB 36 WH	70 W

