



Fugato Fixed MBS250/260, FBS261/270/271/280

Fugato Fixed

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Features

- Optical variation is offered by means of Fugato's dual optic concept: top reflector determining the beam angle and lower optic creating a comfortable lighting effect
- In the Fugato concept there is a seamless transition from the lower optic to the rim, rendering a clean visual articulation of the luminaire for ceiling installation

Application

- Fashion stores
- Chain stores
- Shopping malls
- Departmental stores
- Showrooms
- Offices