



Fugato Fixed MBS250/260, FBS261/270/271/280

Fugato Fixed

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Features

- Optical variation is offered by means of Fugato's dual optic concept: top reflector determining the beam angle and lower optic creating a comfortable lighting effect
- In the Fugato concept there is a seamless transition from the lower optic to the rim, rendering a clean visual articulation of the luminaire for ceiling installation

Application

- Fashion stores
- Chain stores
- Shopping malls
- Departmental stores
- Showrooms
- Offices

Fugato Fixed

Versions



Approval and Application	
Ingress protection code	IP20
Mechanical and Housing	
Color	White

General Information

Order Code	Full Product Name	Compensation circuit	Gear	Lamp family code	Lamp power	Number of light sources	Optic type
911400809080	MBS250 C 1xCDM-TC70W EB 36 WH	-	EB	CDM-TC	70 W	1	36
911400816980	MBS260 C 1xCDM-T70W IC 36 WH	Inductive parallel compensated	CONV	CDM-T	70 W	1	36
911400817080	MBS260 C 1xCDM-T150W IC 36 WH	Inductive parallel compensated	CONV	CDM-T	150 W	1	36
911400820880	FBS261 C 2xPL-C/4P18W HFP C WH	-	EBP	PL-C/4P	18 W	2	C

