



Fugato Fixed MBS250/260, FBS261/270/271/280

Fugato Fixed

The range of Fugato Fixed downlights for general lighting consists of Fugato Compact (cut-out 175mm), Fugato Performance (cut-out 225mm), Fugato Power (cut-out 275mm). It is optically and thermally designed for optimum performance using compact fluorescent lamps and high intensity discharge lamps. A wide range of accessories is available.

Характеристики

- Optical variation is offered by means of Fugato's dual optic concept: top reflector determining the beam angle and lower optic creating a comfortable lighting effect
- In the Fugato concept there is a seamless transition from the lower optic to the rim, rendering a clean visual articulation of the luminaire for ceiling installation

Применение

- Fashion stores
- Chain stores
- Shopping malls
- Departmental stores
- Showrooms
- Offices

Fugato Fixed

Versions



Соответствие требованиям и область применения	
Код защиты от проникновения	IP20
Общая информация	
Количество источников света	1
Тип оптики	36
Механические компоненты и корпус	
Цвет	White

Общая информация

Order Code	Full Product Name	Цепь компенсации	ПРА	Код лампового семейства	Мощность лампы
00808980	MBS250 C 1xCDM-TC35W EB 36 WH	-	EB	CDM-TC	35 W
00809080	MBS250 C 1xCDM-TC70W EB 36 WH	-	EB	CDM-TC	70 W

Order Code	Full Product Name	Цепь компенсации	ПРА	Код лампового семейства	Мощность лампы
00816780	MBS260 1xCDM-T 36D WH	Inductive parallel compensated	CONV	CDM-T	-

