



Compact and robust design

D'ECO Light Collection MBS340/341

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Benefits

- Easy to install
- Wide variety of optical systems
- Fine frame
- High performance

Features

- Aluminum-plate body in white color
- Aluminum reflector with metallic finish
- Round or square frame
- Recessed or surface-mounted
- Options with flat frosted glass, recessed frosted glass or recessed glass with 4 or 9-wing shade
- For the MHN / CDM-TD metal-halide lamp version there is also a chassis with equipment (ballast)

Application

- Ideal for general lighting in shops, hotels and offices

D'ECO Light Collection MBS340/341

Versions

