



MBX/QBX500/502 Scrabble

M/QBX500 Scrabble

Scrabble系列嵌入式筒灯，角度可调节、结构紧凑并有多种光源组合可供选择。可选配 Masterline Hal-R111或 Alu-line Hal-R111光源，也可选配MASTER Color CDM-R30 和 CDM-R20光源。灯具外形根据光源数量不同而定，由单灯、双灯、三灯光源可组成线形灯具，四灯光源则有线形和方形2种不同的灯具外形可选。使用CDM光源时，电器箱需另行订购。

优点

- 充分自由配置1、2、3或4个可调节的多功能灯具
- 单独调节的多功能系统在各个方向提供充分自由的重点照明
- 角度可调节、结构紧凑并有多种光源组合可供选择

特点

- 紧凑型模块化设计，视觉效果佳，是现代商业照明的理想选择
- 选配性能高效的Hal-R111或CDM-R Par20、Par30光源，可为商店创造出合适的氛围
- 同系列产品拥有相同的材质和工艺，易与其他飞利浦商业照明方案相匹配
- 灯具输出LOR：12°:67%
- 颜色：所有灯具都有白色RAL9010和银灰色RAL9006边框可选
- 灯框：QBX500/502采用铝质灯框 厚度仅为3mmMBX500采用铝质灯框
- 灯体：所有灯具都为铁质灯体

应用

- 零售商店
- 酒店
- 安装：推拉式快速安装弹片

规格

M/QBX500 Scrabble


类型	MBX/QBX/CBX 500 (recessed, rectangular version) QBX502 (recessed, square version)
光源	Halogen: - Aluline 111 / G53 / 50 W HID: - MASTERColour CDM-T / G12 / 35, 70 W - MASTERColour CDM-R PAR30 / E27 / 35, 70 W - MASTERColour CDM-R PAR20 / E27 / 35 W - MASTERColour CDM-R111 70 W
光束角	12 to 24° (only for CDM-T)
包括光源	No
灯管位置	Vertical

光学	Narrow beam (12°) Medium beam (24°) only for CDM-T
定位	Cardanic swivel system on two axis to adjust 35° in all directions
颜色	White (WH) RAL colors available on request
材质	Aluminum and steel
安装	Fixation by means of spring fasteners Maintenance: direct lamp acces or after removing the front glass
附件	Electronic transformer, magnetic transformer, gear box
备注	Transformer and gear box to be ordered separately according to lamp type
主要应用	Retail

Versions



二维绘图



Product	H	L	W
QBX500 C 3xHAL-R111-50W ET SI	150 mm	448 mm	204 mm

