



Compact and robust design

D'ECO Light Collection MCS321

The D'ECO Light Collection range offers distinctive design and a wide variety of models and formats. With a compact and discreet design, it maintains the same consistent look throughout the range and offers several optical system options, from glass to anti-glare shades. Easy to install and highly flexible, it can be adjusted to accommodate different-sized lamps with the same luminaire.

Benefits

- Easy to install
- Wide variety of optical systems
- Fine frame
- High performance

Features

- Aluminum-plate body in white color
- Aluminum reflector with metallic finish
- Round or square frame
- Recessed or surface-mounted
- Options with flat frosted glass, recessed frosted glass or recessed glass with 4 or 9-wing shade
- For the MHN / CDM-TD metal-halide lamp version there is also a chassis with equipment (ballast)

Application

- Ideal for general lighting in shops, hotels and offices

Specifications

Type	MCS321	Light source	1 x 70 W, 1 x 150 W / MHN-TD
------	--------	--------------	------------------------------

D'ECO Light Collection MCS321

	1 x 70 W, 1 x 150 W / CDM-TD
Mains voltage	Electromagnetic (high power factor): 220 V / 60 Hz Independent: electronic 220 V / 60-50 Hz
Optical cover	Frosted recessed glass

Materials and finishing	Aluminum-plate body Aluminum reflector and shades with metallic finish
Installation	Surface-mounted on the ceiling

Versions



Operating and Electrical

Input Voltage	220 V
----------------------	-------

General Information

Optical cover/lens type	Glass frosted
Number of light sources	1 pc

Mechanical and Housing

Color	White
--------------	-------

General Information

Order Code	Full Product Name	Lamp family		
		Gear	code	Lamp power
919406005171	MCS321 1XMHN-TD70W/842 220V-60HZ GF WH	-	MHN-TD	70 W
919406005181	MCS321 1XMHN-TD150W/842 220V-60HZ GF WH	-	MHN-TD	150 W

Order Code	Full Product Name	Lamp family		
		Gear	code	Lamp power
919406005191	MCS321 1XCDM-TD70W/942 EB GF WH	EB	CDM-TD	70 W
919406005201	MCS321 1XCDM-TD150W/942 EB GF WH	EB	CDM-TD	150 W

