



UnicOne Projector – Powerful effects

UnicOne Projector Micro MCS/MRS541 C

The UnicOne Projector range offers powerful lighting accents in a small, appealing package, making it ideal for retail and hospitality areas. The Projector adds a sophisticated adjustment rod and hinge to the unique UnicOne design concept. Thanks to its simple design, the UnicOne Projector can be integrated into a variety of environments. The range is designed around the most efficient Elite compact HID and MASTER halogen lamps. The Micro version incorporates MASTERColour CDM-Tm Mini 20/35 W and Masterline halogen lamps, while the Mini version offers higher lumen packages in a compact housing and different accessories. The MiniR111 provides not only strong lighting effects but also good glare control. With such a full range, you certainly have no shortage of choice!

Benefits

- Simple design ensures versatility in application
- Designed around highly efficient Elite compact HID and MASTER halogen lamps
- Full range offering extensive choice

Features

- Micro version – MASTERColour CDM-Tm Mini 20/35 W and Masterline halogen lamps
- Mini version i– MASTERColour CDM-Tc Elite 35/70 W and Masterline halogen lamps
- MiniR111 version – CDM-R111 and Masterline 111/60 W lamps
- Adjustment rod and hinge

Application

- Retail
- Museums
- Exhibition areas
- Public areas

Specifications

UnicOne Projector Micro MCS/MRS541 C

Type	MRS/LRS541 (Micro, 1-circuit track version)
	MCS/LCS541 (Micro, baseplate version)
Light source	MRS/MCS541
	- HID: 1 x MASTERColour CDM-Tm Mini / PGJ5 / 20, 35 W
	LRS/LCS541
	- Halogen: 1 x MASTERLine ES / GU5.3 / 45 W
Lamp beam angle	MASTERLine and MASTERLine 111: 8, 24, 36°
Lamp included	No
Lamp position	Vertical
Light distribution	Direct (D)
Ballast	Electronic, High Frequency 220-240 V / 50-60 Hz:
	- Electronic (EB) for HID lamp version
Transformer	Electronic (ET) for halogen lamp version

Optic	Beam angle 12 to 36° (12-36)
	Reflector narrow beam 12° (R-NB12)
	Reflector medium beam 24° (R-MB24)
	Reflector medium beam 36° (R-MB36)
Connection	3-pole mains
Material	Housing: die-cast aluminum
	Glass, tempered
Color	White (WH), black (BK) or grey (GR)
Installation	Direct on ceiling; baseplate with connection point (BA)
	1-circuit track mounted
Accessories	Protection glass, sculptural lens, UV filters, honey comb louvres and barndoors

Versions



UnicOne LRS541 Projector Micro 1-circuit track version

