



M/SMF283 Tango

Tango MMF283

Compact, sturdy floodlight complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. All-weather construction designed for simple cleaning and speedy servicing.

Benefits

- simple cleaning

Features

- High-grade symmetrical, asymmetrical or parabolic reflector projects a highly efficient light beam
- Wall, ceiling and surface mountings with wide range of adjustments for both down and up lighting
- Quick, easy access to lamp and gear, without affecting beam adjustment, through hinged front window with quick-release clips
- Housing dustproof and jetproof; no internal cleaning required

Application

- Billboard lighting
- Lighting of building facades
- Area and security lighting

Tango MMF283

Versions



MMF283/SMF283

