



MMF383 Tango

Tango MMF383

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

Benefits

- simple cleaning and speedy servicing

Features

- High-grade symmetrical or asymmetrical reflector projects a highly efficient light beam
- Wall, ceiling and surface mountings with wide range of adjustments for both down and up lighting
- Quick, easy access to lamp and gear, without affecting beam adjustment, through hinged front window with quick-release clips
- Housing dustproof and jetproof; no internal cleaning required

Application

- Billboard lighting
- Lighting of building facades
- Area and security lighting

Tango MMF383

Versions



General Information	
Cap-Base	E40
Gear	SGR
Lamp family code	SON-T
Number of light sources	1
Optic type	Symmetrical
Mechanical and Housing	
Colour	-

General Information

Order Code	Full Product Name	Lamp power
910403333801	SMF383 SON-T250W K 240V-50Hz S	250 W

Order Code	Full Product Name	Lamp power
910403334001	SMF383 SON-T400W K 240V-50Hz S	400 W

