



# MMF383 Tango

## Tango MMF383

A compact and sturdy family of floodlights complete with integral gear, particularly suited for surface lighting using metal halide or high-pressure sodium lamps. Its all-weather construction is designed for simple cleaning and speedy servicing.

### Benefits

- simple cleaning and speedy servicing

### Features

- High-grade symmetrical or asymmetrical reflector projects a highly efficient light beam
- Wall, ceiling and surface mountings with wide range of adjustments for both down and up lighting
- Quick, easy access to lamp and gear, without affecting beam adjustment, through hinged front window with quick-release clips
- Housing dustproof and jetproof; no internal cleaning required

### Application

- Billboard lighting
- Lighting of building facades
- Area and security lighting

# Tango MMF383

## Versions



### General Information

Number of light sources	1
-------------------------	---

## General Information

Order Code	Full Product Name	Cap-Base	Gear	Lamp family code	Lamp power	Optic type
910401965080	MMF383 SON-T250W 220V WB YE	-	CONV	SON-T	250 W	Wide beam
910401965280	MMF383 HPI-TP250W 220V WB YE	-	CONV	HPI-TP	250 W	Wide beam
910401965380	MMF383 HPI-TP400W 220V WB YE	-	CONV	HPI-TP	400 W	Wide beam
910403334001	SMF383 SON-T400W K 240V-50Hz S	E40	SON gear	SON-T	400 W	Symmetrical
910403334401	MMF383 HPI-TP400W K 240V-50Hz S	E40	HPL/HPI gear	HPI-TP	400 W	Symmetrical

## Mechanical and Housing

Order Code	Full Product Name	Colour
910401965080	MMF383 SON-T250W 220V WB YE	Yellow
910401965280	MMF383 HPI-TP250W 220V WB YE	Yellow
910401965380	MMF383 HPI-TP400W 220V WB YE	Yellow

Order Code	Full Product Name	Colour
910403334001	SMF383 SON-T400W K 240V-50Hz S	-
910403334401	MMF383 HPI-TP400W K 240V-50Hz S	-

