



Versebay Elite – highly efficient high-bay system solution

VerseBay Elite MPK518

Manufacturing customers want energy-efficient lighting solutions to help ensure their factories are green. Versebay Elite is a high-bay luminaire incorporating high-efficacy CDM Elite lamp technology, as well as extremely efficient gear, which almost halves energy consumption compared with a conventional metal-halide solution. It also provides brilliant lighting performance with excellent color rendering. Versebay Elite's choice of wide and narrow beams makes it suitable for a variety of applications. The luminaire's robust construction and high ingress protection also mean it can be deployed in the most demanding, heavy-duty working environments.

Benefits

- Energy-efficient
- Excellent lighting performance
- Robust, versatile solution

Features

- CDM Elite efficacy 115-120 lm/W
- PrimoVision driver efficacy 92%, with good thermal control; power factor over 0.98
- Well-designed optic; fixture light output ratio 76%
- Color rendering > 90
- IP65

Application

- Industry
- Retail

Specifications

VerseBay Elite MPK518

Type	MPK518
Light source	HID: - 1 x Master colour Elite CDM-TMW / PGZ18 / 210-315 W
Lamp included	No
Ballast	Electronic, High Frequency 220-240 V / 50-60 Hz: - Electronic (EB)
Reflector	Hammerbow (HB)
Optic	Wide beam (WB) Narrow beam (NB)
Optical cover	GPK518, to be ordered separately

Connection	Wieland/Adels push-in connector, 3-pole mains (and 2-pole control signal)
Material	Housing: die-cast aluminium, black-powder coated Reflector: anodised aluminium Optical cover: tempered glass Gasket: silicon
Installation	Individual; in line or in a configuration, suspended mounting with various suspension sets or tubing Operating temperature: -20°C < T
Accessories	Mounting hook (to be ordered separately, if required)

Product details



Accessories



GPK518

Ordercode 911401504501

