



En optimal kombinasjon av verdi og ytelse, MASTER Value LEDspot MV passer perfekt for punktbelysning

MASTER VALUE LEDspot MV

MASTER LEDspot MV gir en halogenaktig lys ideell for spotbelysning (baner, korridorer, heisområder, lobbyer, utstillingsmontre og kabinetter) i servicesektoren. Den er spesielt godt egnet i fellesområder, for eksempel lobbyer, korridorer, og trappeoppganger, der lyset er på døgnet rundt. MASTER LEDspot MV gir store energibesparelser og minimaliserer vedlikeholdskostnadene uten å gå på bekostning av lysstyrken. Dette gjør det mulig for eiere i servicesektoren å spare inn investeringskostnadene i løpet av et år. MASTER LEDspot MV er kompatibel med de fleste armaturer på markedet med GU10-holderen og kan erstatte 35 og 50 W halogenlys-kilder.

Fordeler

- Med MASTER VALUE spotlight opptil 80 % energibesparelse sammenlignet med halogenlamper
- Beste etterligning av halogenspotlight for å skape stemning
- Perfekt erstatning for tradisjonelle GU10-lamper

MASTER VALUE LEDspot MV

Funksjoner

- Dimmeområde
- Kompatibel med en rekke dimmere
- Patentert intelligent driver
- Levetid på 25 000 timer
- Den kjølige lyskjeglen uten UV eller IR er godt egnet for å belyse varmesensitive objekter (mat, organiske materialer, malerier og så videre).



Søknad

- Hotell- og restaurantnæringen
- Detaljhandel
- Boligområder

Warnings and safety

- Driftstemperatur mellom -20 C og 45 C
- Skal bare brukes i tørre eller fuktige omgivelser med nok plass rundt lyskilden (10 mm)

Målskisse



Product	D	C
MAS LED spot VLE D 3.7-35W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE D 4.9-50W GU10 940 60D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 930 36D	50 mm	54 mm
MAS LED spot VLE D 6.2-80W GU10 940 36D	50 mm	54 mm
MAS LED spot VLE DT 4.9-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 6.2-80W GU10 927 36D	50 mm	56 mm

Product	D	C
MAS LED spot VLE D 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 927 60D	50 mm	54 mm
MAS LED spot VLE D 3.7-35W GU10 930 60D	50 mm	54 mm
MAS LED spot VLE D 4.8-50W GU10 927 36D	50 mm	54 mm
MAS LED spot VLE DT 3.7-35W GU10 927 36D	50 mm	54 mm
MAS LEDspot VLE D 4.7-50W GU10 82736D5CT	50 mm	54 mm
MAS LEDspot VLE D 4.7-50W GU10 83036D5CT	50 mm	54 mm

MASTER VALUE LEDspot MV

Generell informasjon

Sokkelbase	GU10
Brytersyklus	50 000
Nominell levetid	25 000 time(r)

Teknisk belysning

Nominell vedlikeholdsfaktor for lyskildelumen ved utgangen av nominell levetid (nom.)	70 %
---	------

Drift og elektronikk

Inngangsfrekvens	50 til 60 Hz
Line Frequency	50 to 60 Hz
Starttid (nom.)	0,5 s

Kontroller og dimming

Kan dimmes	Kun med bestemte dimmere
------------	--------------------------

Mekanikk og innfatning

Lyspæreform	PAR16
-------------	-------

Teknisk belysning (1/2)

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korrelert		
			fargetemperatur (nom)	Fargegjengivelsesindeks (CRI)	Fargekode
67541700	MASTER LED spot VLE D 6.2-80W GU10 927 36D	36 grad(er)	2700 K	90	927
66271400	MASTER LED spot VLE DT 6.2-80W GU10 927 36D	36 grad(er)	2700 K	90	922-927
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	36 grad(er)	4000 K	90	940
70525100	MASTER LED spot VLE D 6.2-80W GU10 930 36D	36 grad(er)	3000 K	90	930
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	36 grad(er)	3000 K	90	930
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	36 grad(er)	4000 K	90	940
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	60 grad(er)	4000 K	90	940
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	36 grad(er)	3000 K	90	930
70789000	MASTER LED spot VLE D 4.9-50W GU10 940 36D	36 grad(er)	4000 K	90	940
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	60 grad(er)	2700 K	90	927
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	60 grad(er)	3000 K	90	930
70795100	MASTER LED spot VLE D 4.9-50W GU10 940 60D	60 grad(er)	4000 K	90	940
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	36 grad(er)	2700 K	90	922-927
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	36 grad(er)	2700 K	90	927
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	36 grad(er)	2200 K	90	922-927
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	60 grad(er)	2700 K	90	927

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Spredningsvinkel (nom.)	Korrelert		
			fargetemperatur (nom)	Fargegjengivelsesindeks (CRI)	Fargekode
31230200	MASTER LED spot VLE D 3.7-35W GU10 930 60D	60 grad(er)	3000 K	90	930
30813800	MASTER LED spot VLE D 4.8-50W GU10 927 36D	36 grad(er)	2700 K	90	927
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	36 grad(er)	2700 K	80	827
31214200	MASTER LEDspot VLE D 4.7-50W GU10 83036D5CT	36 grad(er)	3000 K	80	830

Teknisk belysning (2/2)

Order Code	Full Product Name	Lysytelse	Lysintensitet (nom.)	Order Code	Full Product Name	Lysytelse	Lysintensitet (nom.)
67541700	MASTER LED spot VLE D 6.2-80W GU10 927 36D	575 lm	850 cd	70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	365 lm	400 cd
66271400	MASTER LED spot VLE DT 6.2-80W GU10 927 36D	575 lm	950 cd	70795100	MASTER LED spot VLE D 4.9-50W GU10 940 60D	380 lm	400 cd
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	575 lm	850 cd	70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	355 lm	650 cd
70525100	MASTER LED spot VLE D 6.2-80W GU10 930 36D	575 lm	850 cd	30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	270 lm	500 cd
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	270 lm	500 cd	31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	270 lm	500 cd
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	285 lm	500 cd	31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	270 lm	300 cd
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	285 lm	350 cd	31230200	MASTER LED spot VLE D 3.7-35W GU10 930 60D	270 lm	300 cd
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	365 lm	650 cd	30813800	MASTER LED spot VLE D 4.8-50W GU10 927 36D	355 lm	650 cd
70789000	MASTER LED spot VLE D 4.9-50W GU10 940 36D	380 lm	700 cd	31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	345 lm	650 cd
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	355 lm	400 cd	31214200	MASTER LEDspot VLE D 4.7-50W GU10 83036D5CT	345 lm	650 cd

Drift og elektronikk

Order Code	Full Product Name	Effekten som		Order Code	Full Product Name	Effekten som	
		Effektforbruk	tilsvarer			Effektforbruk	tilsvarer
67541700	MASTER LED spot VLE D 6.2-80W GU10 927 36D	6,2 W	80 W	70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	3,7 W	35 W
66271400	MASTER LED spot VLE DT 6.2-80W GU10 927 36D	6,2 W	80 W	70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	3,7 W	35 W
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	6,2 W	80 W	70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	3,7 W	35 W
70525100	MASTER LED spot VLE D 6.2-80W GU10 930 36D	6,2 W	80 W	70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	4,9 W	50 W

MASTER VALUE LEDspot MV

Order Code	Full Product Name	Effekten som	
		Effektforbruk	tilsvarer
70789000	MASTER LED spot VLE D 4.9-50W GU10 940 36D	4,9 W	50 W
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	4,9 W	50 W
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	4,9 W	50 W
70795100	MASTER LED spot VLE D 4.9-50W GU10 940 60D	4,9 W	50 W
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	4,9 W	50 W
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	3,7 W	35 W

Order Code	Full Product Name	Effekten som	
		Effektforbruk	tilsvarer
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	3,7 W	35 W
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	3,7 W	35 W
31230200	MASTER LED spot VLE D 3.7-35W GU10 930 60D	3,7 W	35 W
30813800	MASTER LED spot VLE D 4.8-50W GU10 927 36D	4,8 W	50 W
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	4,7 W	50 W
31214200	MASTER LEDspot VLE D 4.7-50W GU10 83036D5CT	4,7 W	50 W

Temperatur



Order Code	Full Product Name	Maksimal temperatur for innfatningen (nom.)
67541700	MASTER LED spot VLE D 6.2-80W GU10 927 36D	80 °C
66271400	MASTER LED spot VLE DT 6.2-80W GU10 927 36D	75 °C
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	80 °C
70525100	MASTER LED spot VLE D 6.2-80W GU10 930 36D	80 °C
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	80 °C
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	80 °C
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	80 °C
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	80 °C
70789000	MASTER LED spot VLE D 4.9-50W GU10 940 36D	80 °C
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	80 °C
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	80 °C

Order Code	Full Product Name	Maksimal temperatur for innfatningen (nom.)
70795100	MASTER LED spot VLE D 4.9-50W GU10 940 60D	80 °C
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	80 °C
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	70 °C
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	70 °C
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	70 °C
31230200	MASTER LED spot VLE D 3.7-35W GU10 930 60D	70 °C
30813800	MASTER LED spot VLE D 4.8-50W GU10 927 36D	80 °C
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	80 °C
31214200	MASTER LEDspot VLE D 4.7-50W GU10 83036D5CT	80 °C











Godkjenning og bruksområde

Order Code	Full Product Name	Energiforbruk kWh/1000 t
67541700	MASTER LED spot VLE D 6.2-80W GU10 927 36D	7 kWh
66271400	MASTER LED spot VLE DT 6.2-80W GU10 927 36D	7 kWh
70523700	MASTER LED spot VLE D 6.2-80W GU10 940 36D	7 kWh
70525100	MASTER LED spot VLE D 6.2-80W GU10 930 36D	7 kWh
70775300	MASTER LED spot VLE D 3.7-35W GU10 930 36D	4 kWh
70777700	MASTER LED spot VLE D 3.7-35W GU10 940 36D	4 kWh
70783800	MASTER LED spot VLE D 3.7-35W GU10 940 60D	4 kWh
70787600	MASTER LED spot VLE D 4.9-50W GU10 930 36D	5 kWh
70789000	MASTER LED spot VLE D 4.9-50W GU10 940 36D	5 kWh
70791300	MASTER LED spot VLE D 4.9-50W GU10 927 60D	5 kWh
70793700	MASTER LED spot VLE D 4.9-50W GU10 930 60D	5 kWh
70795100	MASTER LED spot VLE D 4.9-50W GU10 940 60D	5 kWh
70811800	MASTER LED spot VLE DT 4.9-50W GU10 927 36D	5 kWh
30811400	MASTER LED spot VLE D 3.7-35W GU10 927 36D	4 kWh
31228900	MASTER LED spot VLE DT 3.7-35W GU10 927 36D	4 kWh


Order Code	Full Product Name	Energiforbruk kWh/1000 t
31226500	MASTER LED spot VLE D 3.7-35W GU10 927 60D	4 kWh
31230200	MASTER LED spot VLE D 3.7-35W GU10 930 60D	4 kWh
30813800	MASTER LED spot VLE D 4.8-50W GU10 927 36D	5 kWh
31212800	MASTER LEDspot VLE D 4.7-50W GU10 82736D5CT	5 kWh
31214200	MASTER LEDspot VLE D 4.7-50W GU10 83036D5CT	5 kWh




MASTER VALUE LEDspot MV




Accent Diagrams




Accent Diagram - MAS LED spot VLE DT
4.9-50W GU10 927 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 930 36D




Accent Diagram - MAS LED spot VLE D
4.9-50W GU10 940 60D




Accent Diagram - MAS LED spot VLE DT
3.7-35W GU10 927 36D



Accent Diagram - MAS LED spot VLE D 6.2-80W
GU10 940 36D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 60D




Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 930 60D


Accent Diagrams




Accent Diagram - MAS LEDspot VLE D 4.7-50W
GU10 83036D5CT




Accent Diagram - MAS LED spot VLE DT
6.2-80W GU10 927 36D



Accent Diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 4.8-50W
GU10 927 36D




Accent Diagram - MAS LED spot VLE D 6.2-80W
GU10 930 36D


Beam Diagrams



Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 4.9-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 940 36D


Beam Diagrams




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 940 60D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 930 36D




Beam diagram - MAS LED spot VLE D 4.9-50W
GU10 940 60D




Beam diagram - MAS LED spot VLE DT 6.2-80W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 6.2-80W
GU10 930 36D




Beam diagram - MAS LEDspot VLE D 4.7-50W
GU10 83036D5CT



Beam diagram - MAS LED spot VLE D 4.8-50W
GU10 927 36D




Beam diagram - MAS LED spot VLE DT 3.7-35W
GU10 927 36D




Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 930 60D

MASTER VALUE LEDspot MV

Beam Diagrams



Beam diagram - MAS LED spot VLE D 3.7-35W
GU10 927 60D



Beam diagram - MAS LED spot VLE D 6.2-80W
GU10 940 36D

