



OptiFlood – compact and complete solution

OptiFlood Mini MVP504

Philips has a long tradition of excellence in environmentally friendly asymmetric floodlighting systems for sports and general area lighting as well as architectural applications. OptiFlood's extremely efficient, best-in-class optical system provides an accurately controlled light distribution – total light cut-off above the horizontal and a peak beam intensity at high angles – keeping obtrusive light to a minimum. Both the MVP504 and MVP506 versions are available with two types of reflector – asymmetric or road-lighting POT optics – for flexibility in application. They can also accommodate CosmoPolis metal-halide lamps for good color rendering, high-pressure sodium lamps for economical operation, and MASTERColour CDM Elite MW lamps for highly efficient lighting with longer-lasting white light. OptiFlood is also available in a LED version (BVP506). With its compact shape and aesthetically pleasing design, OptiFlood can be used in applications where design and appearance are just as important as technical performance. In the design, attention has also been focused on the detailing. This has led to integrated 'hidden' hinges, angle adjustment designed as part of the body and a mounting bracket angled to allow more aesthetic integration onto columns.

Benefits

- Asymmetrical floodlighting systems for general area lighting as well as security and industrial area lighting
- Best-in-class optical system for accurately controlled light distribution to prevent uncontrolled stray and spill light
- Compact shape and pleasing design allows OptiFlood to be used in settings where design and appearance are just as important as technical performance

OptiFlood Mini MVP504

Features

- Two types of reflector – asymmetric or road-lighting POT optics
- Can accommodate CosmoPolis metal-halide lamps, high-pressure sodium lamps, and MASTERColour CDM Elite MW lamps
- Also available in a LED version
- Two body sizes

Application

- General area lighting
- Car parks
- Architectural floodlighting
- Sports lighting

Specifications

Type	MVP504	Color	'Raw' aluminum or ultra-dark grey (GR) Other RAL colors available on request
Light source	HID: <ul style="list-style-type: none">- 1 x MASTERColour CDM-TD / RX7s / 70, 150 W- 1 x MASTERColour CDM-T / G12 / 35, 70 W- 1 x MASTER CosmoWhite CPO-TW / PGZ12 / 45, 60, 90, 140 W- 1 x MASTER CityWhite CDO-TT / E27 / 70 W- 1 x MASTER SON-T PIA Plus / E27 / 50, 70 W	Installation	On mast head frame, ceiling, wall and floor mounting Front cover hinges for easy access Aiming indicator ring is integrated on housing and bracket Ambient temperature outdoor: 35°C (25°C indoor) Recommended mounting height: 4 - 6 m Adjustable tilt angle: 15° CosmoPolis optic (OC): 6 positions Max windage area: 0.04 m Max SCx value by side: 0.037 m Max adjustment from the horizontal: - 180 to +180° Max vertical aiming: - 90 to +105° Uplighting for indoor only
Lamp included	Yes (K or light color 828 or 942)	Maintenance	Lamp and gear unit access by opening the hinged front glass for in position lamp replacement No internal cleaning required
Ballast (integrated)	Electromagnetic 230 or 240 V / 50 Hz Electronic, 220-240 V / 50-60 Hz: <ul style="list-style-type: none">- Electronic (EB)	Accessories	Wire guard Styled pole mounting brackets (single, double, triple and quadruple) available on request
Optic	CosmoPolis open optic R60 (OC) Facetted road lighting POT (OR) for 35 and 70 W CDM-T lamp versions Asymmetrical (A) for 45-140 W lamp versions, except CDM-T lamp version	Main applications	General area, car parks, architectural floodlighting
Ignitor	Semi-parallel, self-stopping (ST)		
Options	Safety class 2		
Materials and finishing	Housing: high-pressure die-cast aluminum, non-corrosive Glass: thermally hardened, 4 mm thick Clips: stainless steel Reflector: purity, anodized aluminum, high reflective		

Versions

OptiFlood Mini MVP504 area-lighting
luminaire



OptiFlood Mini MVP504

Product details

Front cover is held in place by two stainless steel clips, and can be released easily using a screwdriver




When opened, front cover hinges back to provide full access to gear and lamp compartment



When opened, front cover hinges back to provide full access to gear and lamp compartment



Front cover fully open, providing excellent access to all components



Connector



CosmoPolis optic



Facetted road-lighting POT optic



Facetted road-lighting POT optic

OptiFlood Mini MVP504

Product details



Asymmetrical optic



Asymmetrical optic

Approval and Application

Mech. impact protection code IK08

General Information

CE mark	CE mark
Light source colour	942 neutral white
Optical cover/lens type	GC
ENEC mark	-
Gear	EB
Lamp family code	CDM-TD
Number of light sources	1
Optic type	Asymmetrical
Product Family Code	MVP504

General Information

Order Code	Full Product Name	Lamp power
910403760012	MVP504 CDM-TD150W/942 EB I A	150 W
910403763212	MVP504 CDM-TD150W/942 EB I A GR	150 W
910403764512	MVP504 CDM-TD70W/942 EB II A GR	70 W

Mechanical and Housing

Order Code	Full Product Name	Colour
910403760012	MVP504 CDM-TD150W/942 EB I A	-
910403763212	MVP504 CDM-TD150W/942 EB I A GR	Grey

Order Code	Full Product Name	Colour
910403764512	MVP504 CDM-TD70W/942 EB II A GR	Grey

