



Enabling future proof OLED technology

Lumiblade OLED Driver-Low Voltage

This driver detects the power and voltage needs of the attached OLED and drives the attached OLED Panel accordingly. This one-driver-fits-all-panels approach eases the life of the customers and makes this driver also compatible for future developments.

Benefits

- 0-10V or DALI controller dimming down to 1%
- A protection circuit for the OLED is implemented
- Compact housing enables new design possibilities
- Cascading multiple drivers reduces the costs for the transformers

Features

- Small dimensions
- Operating window from 100 to 400 mA, adjustable by OLED resistor or software programmable
- DALI and 0-10 Volt control interface in one driver
- 24 Volt DC input

Application

- Offices, integrating light into products Furniture


Lumiblade OLED Driver-Low Voltage

Versions



Lumiblade OLED Driver-Low Voltage

Versions






Dimensional drawing



Product	D1	A2	B2	C1	A1	A3	X1	B1
Xitanium 150W 0.70A 230V sXt	8 mm	226.2 mm	42.9 mm	37.1 mm	240.5 mm	211.1 mm	280 mm	59.1 mm
XITANIUM 75W 0.35-0.70 GL PROG+SD SXT	8.0 mm	226.2 mm	42.9 mm	37.1 mm	240.5 mm	211.1 mm	500 mm	59.1 mm
Xitanium 150W .35/.41/.53 1-10V 230V sXt	8 mm	226.2 mm	42.9 mm	37.1 mm	240.5 mm	211.1 mm	500 mm	59.1 mm
XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	8.0 mm	226.2 mm	42.9 mm	37.1 mm	240.5 mm	211.1 mm	500 mm	59.1 mm

Lumiblade OLED Driver-Low Voltage

Dimensional drawing



Product	B2	C1	A1	A2	B1
XITANIUM 75W 1.05A 0-10V INT-Y	42.9 mm	38 mm	168 mm	153 mm	59.1 mm


Product	D1	A2	B2	C1	A1	A3	X1	B1
XITANIUM 100W	5.5	155	50	38	165	147.4	275	70
0.53A PROG+ GL-	mm	mm	mm	mm	mm	mm	mm	mm
Z sXt								

Product	C1	A1	A2	A3	B1
XITANIUM 30W 0.52A 60V	30.0 mm	106.7 mm	115.6 mm	50.8 mm	76.2 mm
0-10V INTELLIVOLT					
XITANIUM 39W 0.52A 80V	30.0 mm	106.7 mm	115.6 mm	50.8 mm	76.2 mm
0-10V INTELLIVOLT					


Product	C1	A1	A2	A3	B1
XITANIUM 75W 0.53A AOC	38.1 mm	167.4 mm	153.2 mm	138.2 mm	59.2 mm
INT-Y SXT					
XITANIUM 75W 0.53A 0-10V	38.1 mm	167.4 mm	153.2 mm	138.2 mm	59.2 mm
INT-Y SXT					

Lumiblade OLED Driver-Low Voltage

Dimensional drawing



A2



Product	C1	A1	A2	A3	B1
XITANIUM 2X50W 1.5A 0-10V -H SXT	38.1 mm	160.5 mm	151.4 mm	143.8 mm	91.4 mm


Product	C1	A1	A2	B1
XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	25.4 mm	358.1 mm	350.0 mm	30.0 mm
XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	25.4 mm	358.1 mm	350.0 mm	30.0 mm

Product	D1	A2	C1	A1	B1
Xitanium 30W 400mA 76V 230V	4.1 mm	265.0 mm	22.0 mm	280.0 mm	30.0 mm

Product	C1	A1	A2	B1
XITANIUM 75W 0.7-2.0A 54V TE/ DALI INT	25.4 mm	424.2 mm	415.0 mm	30.0 mm
XITANIUM 75W 0.7-2.0A 54V TE/ 0-10V INT	25.4 mm	424.2 mm	415.0 mm	30.0 mm


Lumiblade OLED Driver-Low Voltage

Dimensional drawing



Product
OLED Panel Brite FL300 ww B1 PCAL

Product	D1	B2	C1	C2	A1	A2	B1
XITANIUM 10W	3.8	24.6	24.9	3.0	132.0	122.4	34.3
0.35A 28V 120V	mm	mm	mm	mm	mm	mm	mm
60HZ OUTDOOR							




Product
XITANIUM 80W 3.3A 24V 120V 60HZ

Product	A2	C1	A1	B1
Driver D024V 10W/0.1-0.4A/28V DMX	50.2 mm	11.5 mm	57.0 mm	58.3 mm

Lumiblade OLED Driver-Low Voltage


Dimensional drawing



A2

Product	D1	A2	C1	A1	B1
Xitanium 40W 0.28A 142V 230V (C)	4.1 mm	265.0 mm	22.0 mm	280.0 mm	30.0 mm

Product	A1	B1	C1
Xitanium 10W 0.6A 16V 230V PCB	76 mm	59 mm	26 mm




Product	A1	A2	B1	C1	D1
Xitanium 15W 0.35A 42V I 230V	115 mm	105 mm	45 mm	29 mm	3.4 mm

Product
Fortimo LED LLM 1100/740 8W Gen4
Fortimo LED LLM 1100/730 9W Gen4
Fortimo LED LLM 3000/730 26W Gen4
Fortimo LED LLM 4500/740 36W Gen4
Fortimo LED LLM 4500/730 39W Gen4
Fortimo LED LLM 1800/730 16W Gen4
Fortimo LED LLM 1800/740 15W Gen4
Fortimo LED LLM 3000/740 24W Gen4


Lumiblade OLED Driver-Low Voltage

Dimensional drawing

Product	C1	C2	A1	A3	B1
Fortimo LED DLM 3000 30W/835 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 3000 29W/840 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 1500 14W/835 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 1100 9W/840 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 2000 21W/830 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 1100 10W/830 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 2000 19W/840 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 1100 10W/835 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 2000 20W/835 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 1500 13W/840 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 3000 32W/830 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm
Fortimo LED DLM 1500 15W/830 UL Gen4	43.7 mm	40.2 mm	81.6 mm	66.8 mm	82.8 mm




Product
InteGrade engine vision 575mm (23") WWR



Product
INTEGRADE FIXTURE VISION 875MM(34IN) 830
InteGrade fixture value 875mm(34") 830

Lumiblade OLED Driver-Low Voltage

Dimensional drawing



R1

Product

Driver D024V 10W/0.1-0.4A/28V D/A

Product	D1	A2	C1	A1	B1
Xitanium 36W/0.12-0.4A 110V 230V	4.1 mm	265.0 mm	22.0 mm	280.0 mm	30.0 mm

Approval and Application

Order Code	Full Product Name	IP Classification	Surge Protection (Common/ Differential)
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	-	-
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	-	-
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	-	-
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	-	-
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	IP 66	3/3 kV
91370267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	-	-
913710859002	Xitanium 150W 0.70A 230V sXt	IP 66	3/3 kV
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-
925400010101	Driver D024V 10W/0.1-0.4A/28V D/A	20	-
925400012002	Driver D024V 10W/0.1-0.4A/28V DMX	20	-
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/ DALI INT	-	-

Order Code	Full Product Name	IP Classification	Surge Protection (Common/ Differential)
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/ 0-10V INT	-	-
929000645913	InteGrade fixture value 875mm(34") 830	-	-
929000867913	INTEGRADE FIXTURE VISION 875MM(34IN) 830	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG+SD SXT	IP 66	4/4 kV
929000705113	XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	IP 66	4/4 kV
929000708113	XITANIUM 2X50W 1.5A 0-10V -H SXT	-	-
929000710403	XITANIUM 100W 0.53A PROG+ GL-Z sXt	-	4/4 kV
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	-	2/2 kV
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	-	2/2 kV
929000711413	XITANIUM 75W 0.53A 0-10V INT- Y SXT	-	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	IP Classification	Surge Protection (Common/ Differential)
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	-	-
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	-
929000805108	Xitanium 40W 0.28A 142V 230V (C)	20	EN61547 (L-L 1kV, L-G 2kV) kV
929000814503	Xitanium 36W/0.12-0.4A 110V 230V	20	-
929000830608	Xitanium 30W 400mA 76V 230V	20	-
929000866113	InteGrade engine vision 575mm (23") WWR	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-

Order Code	Full Product Name	IP Classification	Surge Protection (Common/ Differential)
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	-	4/2 kV
929000941406	Fortimo LED LLM 1100/730 9W Gen4	-	-
929000941506	Fortimo LED LLM 1100/740 8W Gen4	-	-
929000941606	Fortimo LED LLM 1800/730 16W Gen4	-	-
929000941706	Fortimo LED LLM 1800/740 15W Gen4	-	-
929000941806	Fortimo LED LLM 3000/730 26W Gen4	-	-
929000941906	Fortimo LED LLM 3000/740 24W Gen4	-	-
929000942006	Fortimo LED LLM 4500/730 39W Gen4	-	-
929000942106	Fortimo LED LLM 4500/740 36W Gen4	-	-
929001410180	Xitanium 15W 0.35A 42V I 230V	20	EN61547 (L-L 1kV, L-G 2kV) kV
929001417071	Xitanium 10W 0.6A 16V 230V PCB	20	EN61547 (L-L 0.5kV, L-G 1kV) kV

Operating and Electrical

Order Code	Full Product Name	Output Current (Max)	Output Current (Nom)	Output Power (Max)	Output Power (Nom)	Output Voltage	Input Voltage (AC)	Input Voltage (DC)
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	-	3300 mA	-	80 W	24 V	120 V	-
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	-	350-520 mA	-	30 W	20-56 V	120-277 V	-
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	-	350-520 mA	-	40 W	40-77 V	120-277 V	-
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	-	700-1050 mA	-	50 W	25-48 V	120-277 V	-
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	-	350/410/530 mA	-	42-150 W	115-280 V	220-240 V	-
913710267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	-	350 mA	-	10 W	2.8-28 V	120 V	-
913710859002	Xitanium 150W 0.70A 230V sXt	-	700 mA	-	42-150 W	60-210 V	220-240 V	-
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-	-	-	-	-	-
925400010101	Driver D024V 10W/0.1-0.4A/28V D/A	-	100-400 mA	-	10-10 W	1-28 V	-	21.6-26.4 V
925400012002	Driver D024V 10W/0.1-0.4A/28V DMX	-	100-400 mA	-	10-10 W	1-28 V	-	21.6-26.4 V
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/DALI INT	-	700-2000 mA	-	75 W	27-54 V	120-277 V	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	Output Current (Max)	Output Current (Nom)	Output Power (Max)	Output Power (Nom)	Output Voltage	Input Voltage (AC)	Input Voltage (DC)
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/0-10V INT	-	700-2000 mA	-	75 W	27-54 V	120-277 V	-
929000645913	InteGrade fixture value 875mm(34") 830	-	-	-	-	-	-	-
929000867913	INTEGRADE FIXTURE VISION 875MM(34IN) 830	-	-	-	-	-	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG+SD SXT	-	Programmable (350-700) mA	-	30-75 W	80-152 V	120-277 V	-
929000705113	XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	-	Programmable (350-700) mA	-	30-150 W	125-280 V	120-277 V	-
929000708113	XITANIUM 2X50W 1.5A 0-10V -H SXT	-	1500 mA	-	75 W	20-36 V	120-277 V	-
929000710403	XITANIUM 100W 0.53A PROG+ GL-Z sXt	-	100-530 mA	-	35-100 W	94-189 V	120-277 V	-
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	-	700-1500 mA	-	54 W	27-54 V	120 V	-
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	-	700-1500 mA	-	54 W	27-54 V	120-277 V	-
929000711413	XITANIUM 75W 0.53A 0-10V INT-Y SXT	-	530 mA	-	75 W	71-143 V	120-277 V	-
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	-	100-530 mA	-	75 W	71-143 V	120-277 V	-
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	750 mA	-	75 W	-	120-277 V	-
929000805108	Xitanium 40W 0.28A 142V 230V (C)	280 mA	280 mA	40 W	32.5 W	120-138 V	220-240 V	186-250 V
929000814503	Xitanium 36W/0.12-0.4A 110V 230V	-	120-400 mA	-	10-36 W	50-110 V	202-254 V	168-275 V
929000830608	Xitanium 30W 400mA 76V 230V	-	400 mA	-	28-30 W	64-76 V	220-240 V	186-250 V
929000866113	InteGrade engine vision 575mm (23") WWR	-	-	-	-	-	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-	-	-	-	-	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-	-	-	-	-	-
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-	-	-	-	-	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-	-	-	-	-	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-	-	-	-	-	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-	-	-	-	-	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-	-	-	-	-	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-	-	-	-	-	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-	-	-	-	-	-
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-	-	-	-	-	-
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-	-	-	-	-	-
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-	-	-	-	-	-
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	-	100-1000 mA	-	4-70 W	30-100 V	220-240 V	-
929000941406	Fortimo LED LLM 1100/730 9W Gen4	-	-	-	-	-	-	-
929000941506	Fortimo LED LLM 1100/740 8W Gen4	-	-	-	-	-	-	-
929000941606	Fortimo LED LLM 1800/730 16W Gen4	-	-	-	-	-	-	-
929000941706	Fortimo LED LLM 1800/740 15W Gen4	-	-	-	-	-	-	-
929000941806	Fortimo LED LLM 3000/730 26W Gen4	-	-	-	-	-	-	-
929000941906	Fortimo LED LLM 3000/740 24W Gen4	-	-	-	-	-	-	-
929000942006	Fortimo LED LLM 4500/730 39W Gen4	-	-	-	-	-	-	-
929000942106	Fortimo LED LLM 4500/740 36W Gen4	-	-	-	-	-	-	-
929001410180	Xitanium 15W 0.35A 42V I 230V	350 mA	350 mA	15 W	13 W	32-42 V	220-240 V	-
929001417071	Xitanium 10W 0.6A 16V 230V PCB	600 mA	600 mA	9.6 W	8.4 W	12-16 V	220-240 V	-

Temperature (1/2)

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Lifetime (Max)	T-Case Lifetime (Nom)	T-Case Maximum (Max)	T-Case Maximum (Nom)	Module Temperature Protection
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	60 °C	-40 °C	-	-	90 °C	-	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Lifetime (Max)	T-Case Lifetime (Nom)	T-Case Maximum (Max)	T-Case Maximum (Nom)	Module Temperature Protection
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	60 °C	-40 °C	-	-	75 °C	-	-
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	55 °C	-20 °C	-	-	75 °C	-	-
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	55 °C	-40 °C	-	-	85 °C	-	-
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	55 °C	-40 °C	-	67 °C	80 °C	-	Programmable
913710267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	60 °C	-40 °C	-	-	90 °C	-	-
913710859002	Xitanium 150W 0.70A 230V sXt	55 °C	-40 °C	-	67 °C	80 °C	-	-
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-	-	-	-	-	-
925400010101	Driver D024V 10W/0.1-0.4A/28V D/A	50 °C	-20 °C	-	50 °C	85 °C	-	-
925400012002	Driver D024V 10W/0.1-0.4A/28V DMX	50 °C	-20 °C	-	50 °C	85 °C	-	-
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/DALI INT	50 °C	-20 °C	-	-	75 °C	-	-
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/0-10V INT	50 °C	-20 °C	-	-	75 °C	-	-
929000645913	InteGrade fixture value 875mm(34") 830	30 °C	-30 °C	-	-	-	-	-
929000867913	INTEGRADE FIXTURE VISION 875MM(34IN) 830	30 °C	-30 °C	-	-	-	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG+SD SXT	55 °C	-40 °C	-	70 °C	80 °C	-	Programmable
929000705113	XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	55 °C	-40 °C	-	70 °C	80 °C	-	Programmable
929000708113	XITANIUM 2X50W 1.5A 0-10V -H SXT	55 °C	-40 °C	-	-	80 °C	-	-
929000710403	XITANIUM 100W 0.53A PROG+ GL-Z sXt	55 °C	-40 °C	-	66 °C	80 °C	-	Programmable
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	50 °C	-20 °C	-	-	85 °C	-	-
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	50 °C	-20 °C	-	-	85 °C	-	-
929000711413	XITANIUM 75W 0.53A 0-10V INT-Y SXT	55 °C	-40 °C	-	-	80 °C	-	-
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	55 °C	-40 °C	-	-	80 °C	-	-
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	-	-	-	80 °C	-	-
929000805108	Xitanium 40W 0.28A 142V 230V (C)	50 °C	-20 °C	-	75 °C	75 °C	-	-
929000814503	Xitanium 36W/0.12-0.4A 110V 230V	50 °C	-20 °C	65 °C	-	75 °C	-	-
929000830608	Xitanium 30W 400mA 76V 230V	50 °C	-20 °C	-	-	75 °C	-	-
929000866113	InteGrade engine vision 575mm (23") WWR	30 °C	-30 °C	-	-	-	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-20 °C	-	-	-	65 °C	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	T-Ambient (Max)	T-Ambient (Min)	T-Case Lifetime (Max)	T-Case Lifetime (Nom)	T-Case Maximum (Max)	T-Case Maximum (Nom)	Module Temperature Protection
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-20 °C	-	-	-	65 °C	-
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	60 °C	-40 °C	-	75 °C	90 °C	-	Programmable
929000941406	Fortimo LED LLM 1100/730 9W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000941506	Fortimo LED LLM 1100/740 8W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000941606	Fortimo LED LLM 1800/730 16W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000941706	Fortimo LED LLM 1800/740 15W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000941806	Fortimo LED LLM 3000/730 26W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000941906	Fortimo LED LLM 3000/740 24W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000942006	Fortimo LED LLM 4500/730 39W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929000942106	Fortimo LED LLM 4500/740 36W Gen4	55 °C	-20 °C	-	65 °C	-	75 °C	-
929001410180	Xitanium 15W 0.35A 42V I 230V	50 °C	0 °C	-	65 °C	75 °C	-	-
929001417071	Xitanium 10W 0.6A 16V 230V PCB	55 °C	-20 °C	-	-	-	-	-

Temperature (2/2)

Order Code	Full Product Name	T-Case Switch Off (Nom)	T-Storage (Max)	T-Storage (Min)
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	-	-	-
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	-	-	-
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	-	-	-
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	-	-	-
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	94 °C	-	-
913701267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	-	-	-
913701859002	Xitanium 150W 0.70A 230V sXt	80 °C	-	-
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-	-
925400010101	Driver D024V 10W/0.1-0.4A/28V D/A	-	85 °C	-25 °C
925400012002	Driver D024V 10W/0.1-0.4A/28V DMX	-	85 °C	-40 °C
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/DALI INT	-	-	-
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/0-10V INT	-	-	-
929000645913	InteGrade fixture value 875mm(34") 830	-	-	-

Order Code	Full Product Name	T-Case Switch Off (Nom)	T-Storage (Max)	T-Storage (Min)
929000867913	INTEGRADE FIXTURE VISION 875MM(34IN) 830	-	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG+SD SXT	89 °C	-	-
929000705113	XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	87 °C	-	-
929000708113	XITANIUM 2X50W 1.5A 0-10V - H SXT	-	-	-
929000710403	XITANIUM 100W 0.53A PROG+ GL-Z sXt	85 °C	-	-
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	-	-	-
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	-	-	-
929000711413	XITANIUM 75W 0.53A 0-10V INT-Y SXT	-	-	-
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	-	-	-
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	-	-
929000805108	Xitanium 40W 0.28A 142V 230V (C)	-	85 °C	-25 °C
929000814503	Xitanium 36W/0.12-0.4A 110V 230V	-	85 °C	-25 °C
929000830608	Xitanium 30W 400mA 76V 230V	-	85 °C	-25 °C

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	T-Case	T-Storage	T-Storage
		Switch Off (Nom)	(Max)	(Min)
929000866113	InteGrade engine vision 575mm (23") WWR	-	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-	-
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-	-
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-	-
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-	-

Order Code	Full Product Name	T-Case	T-Storage	T-Storage
		Switch Off (Nom)	(Max)	(Min)
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-	-
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	-	50 °C	-30 °C
929000941406	Fortimo LED LLM 1100/730 9W Gen4	-	85 °C	-40 °C
929000941506	Fortimo LED LLM 1100/740 8W Gen4	-	85 °C	-40 °C
929000941606	Fortimo LED LLM 1800/730 16W Gen4	-	85 °C	-40 °C
929000941706	Fortimo LED LLM 1800/740 15W Gen4	-	85 °C	-40 °C
929000941806	Fortimo LED LLM 3000/730 26W Gen4	-	85 °C	-40 °C
929000941906	Fortimo LED LLM 3000/740 24W Gen4	-	85 °C	-40 °C
929000942006	Fortimo LED LLM 4500/730 39W Gen4	-	85 °C	-40 °C
929000942106	Fortimo LED LLM 4500/740 36W Gen4	-	85 °C	-40 °C
929001410180	Xitanium 15W 0.35A 42V I 230V	-	85 °C	-25 °C
929001417071	Xitanium 10W 0.6A 16V 230V PCB	-	85 °C	-25 °C

Wiring (1/2)

Order Code	Full Product Name	Connector Type Input Terminals	Connector Type	Control Wire	Control Wire	Control Wire	Control Wire Length	Hot Wiring
			Output Terminals	Cross Section (Max)	Cross Section (Min)	Cross Section (Nom)		
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	Wago 250	-	-	-	-	-	-
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	-	-	-	-	-	-	-
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	-	-	-	-	-	-	-
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	-	-	-	-	-	-	-
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	-	-	-	-	0.82 mm²	500 mm	-
91370267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	Wago 250	-	-	-	-	-	-
91370859002	Xitanium 150W 0.70A 230V sXt	-	-	-	-	-	-	-
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-	-	-	-	-	-
925400010101	Driver D024V 10W/0.1-0.4A/28V D/A	WAGO 2060-series	-	-	-	-	-	Yes
925400012002	Driver D024V 10W/0.1-0.4A/28V DMX	WAGO 2060-series	-	-	-	-	-	Yes
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/DALI INT	-	-	-	-	-	-	-
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/0-10V INT	-	-	-	-	-	-	-
929000645913	InteGrade fixture value 875mm(34") 830	-	-	-	-	-	-	-
929000867913	INTEGRADE FIXTURE VISION 875MM(34IN) 830	-	-	-	-	-	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG+SD SXT	-	-	-	-	0.82 mm²	500 mm	-
929000705113	XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	-	-	-	-	0.82 mm²	500 mm	-
929000708113	XITANIUM 2X50W 1.5A 0-10V -H SXT	-	-	-	-	-	305.0 mm	-
929000710403	XITANIUM 100W 0.53A PROG+ GL-Z sXt	-	-	-	-	0.82 mm²	275 mm	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	Connector Type		Control Wire Cross Section (Max)	Control Wire Cross Section (Min)	Control Wire Cross Section (Nom)	Control Wire Length	Hot Wiring
		Input Terminals	Output Terminals					
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	-	-	-	-	-	-	-
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	-	-	-	-	-	-	-
929000711413	XITANIUM 75W 0.53A 0-10V INT-Y SXT	-	-	-	-	-	270.0 mm	-
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	-	-	-	-	-	270.0 mm	-
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	-	-	-	-	270.0 mm	-
929000805108	Xitanium 40W 0.28A 142V 230V (C)	Wago 744	Wago 744	-	-	-	-	No
929000814503	Xitanium 36W/0.12-0.4A 110V 230V	Wago 744	Wago 744	-	-	-	-	No
929000830608	Xitanium 30W 400mA 76V 230V	Wago 744	Wago 744	-	-	-	-	No
929000866113	InteGrade engine vision 575mm (23") WWR	-	-	-	-	-	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-	-	-	-	-	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-	-	-	-	-	-
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-	-	-	-	-	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-	-	-	-	-	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-	-	-	-	-	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-	-	-	-	-	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-	-	-	-	-	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-	-	-	-	-	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-	-	-	-	-	-
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-	-	-	-	-	-
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-	-	-	-	-	-
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-	-	-	-	-	-
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	Wago 804	-	2.5 mm ²	0.5 mm ²	-	-	-
929000941406	Fortimo LED LLM 1100/730 9W Gen4	-	-	-	-	-	-	-
929000941506	Fortimo LED LLM 1100/740 8W Gen4	-	-	-	-	-	-	-
929000941606	Fortimo LED LLM 1800/730 16W Gen4	-	-	-	-	-	-	-
929000941706	Fortimo LED LLM 1800/740 15W Gen4	-	-	-	-	-	-	-
929000941806	Fortimo LED LLM 3000/730 26W Gen4	-	-	-	-	-	-	-
929000941906	Fortimo LED LLM 3000/740 24W Gen4	-	-	-	-	-	-	-
929000942006	Fortimo LED LLM 4500/730 39W Gen4	-	-	-	-	-	-	-
929000942106	Fortimo LED LLM 4500/740 36W Gen4	-	-	-	-	-	-	-
929001410180	Xitanium 15W 0.35A 42V I 230V	Wago 250	Wago 250	-	-	-	-	No
929001417071	Xitanium 10W 0.6A 16V 230V PCB	Wago 250	Wago 250	-	-	-	-	No

Wiring (2/2)

Order Code	Full Product Name	Input Wire Cross Section	Output Wire Cross Section (Max)	Output Wire Cross Section (Min)	Output Wire Cross Section (Nom)	Output Wire Length
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	-	-	-	-	660.4 mm
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	-	-	-	-	-
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	-	-	-	-	-

Order Code	Full Product Name	Input Wire Cross Section	Output Wire Cross Section (Max)	Output Wire Cross Section (Min)	Output Wire Cross Section (Nom)	Output Wire Length
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	-	-	-	-	-
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	0.82 mm ²	-	-	0.82 mm ²	500 mm
913701267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	-	-	-	-	152.4 mm

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	Input	Output	Output	Output	Output
		Wire	Wire	Wire	Wire	
		Cross	Cross	Cross	Cross	Length
		Section	(Max)	(Min)	(Nom)	
913710859002	Xitanium 150W 0.70A 230V sXt	0.82 mm²	-	-	0.82 mm²	280 mm
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-	-	-	-
925400010101	Driver D024V 10W/ 0.1-0.4A/28V D/A	-	-	-	-	-
925400012002	Driver D024V 10W/ 0.1-0.4A/28V DMX	-	-	-	-	-
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/ DALI INT	-	-	-	-	-
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/ 0-10V INT	-	-	-	-	-
929000645913	InteGrade fixture value 875mm(34") 830	-	-	-	-	-
929000867913	INTEGRADE FIXTURE VISION 875MM(34IN) 830	-	-	-	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG +SD SXT	0.82 mm²	-	-	0.82 mm²	500 mm
929000705113	XITANIUM 150W 0.35-0.70 GL PROG +SD SXT	0.82 mm²	-	-	0.82 mm²	500 mm
929000708113	XITANIUM 2X50W 1.5A 0-10V -H SXT	-	-	-	-	305.0 mm
929000710403	XITANIUM 100W 0.53A PROG+ GL-Z sXt	0.82 mm²	-	-	0.82 mm²	275 mm
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	-	-	-	-	-
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	-	-	-	-	-
929000711413	XITANIUM 75W 0.53A 0-10V INT-Y SXT	-	-	-	-	270.0 mm
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	-	-	-	-	270.0 mm
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	-	-	-	270.0 mm
929000805108	Xitanium 40W 0.28A 142V 230V (C)	-	1.5 mm²	0.5 mm²	-	-

Order Code	Full Product Name	Input	Output	Output	Output	Output
		Wire	Wire	Wire	Wire	
		Cross	Cross	Cross	Cross	Length
		Section	(Max)	(Min)	(Nom)	
929000814503	Xitanium 36W/ 0.12-0.4A 110V 230V	-	-	-	-	-
929000830608	Xitanium 30W 400mA 76V 230V	-	-	-	-	-
929000866113	InteGrade engine vision 575mm (23") WWR	-	-	-	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-	-	-	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-	-	-	-
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-	-	-	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-	-	-	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-	-	-	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-	-	-	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-	-	-	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-	-	-	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-	-	-	-
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-	-	-	-
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-	-	-	-
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-	-	-	-
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	-	-	-	-	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	Input	Output	Output	Output	Output Wire Length
		Wire	Wire	Wire	Wire	
		Cross	Cross	Cross	Cross	
		Section	Section	Section	Section	
		(Max)	(Min)	(Nom)		
929000941406	Fortimo LED LLM 1100/730 9W Gen4	-	-	-	-	-
929000941506	Fortimo LED LLM 1100/740 8W Gen4	-	-	-	-	-
929000941606	Fortimo LED LLM 1800/730 16W Gen4	-	-	-	-	-
929000941706	Fortimo LED LLM 1800/740 15W Gen4	-	-	-	-	-
929000941806	Fortimo LED LLM 3000/730 26W Gen4	-	-	-	-	-

Order Code	Full Product Name	Input	Output	Output	Output	Output Wire Length
		Wire	Wire	Wire	Wire	
		Cross	Cross	Cross	Cross	
		Section	Section	Section	Section	
		(Max)	(Min)	(Nom)		
929000941906	Fortimo LED LLM 3000/740 24W Gen4	-	-	-	-	-
929000942006	Fortimo LED LLM 4500/730 39W Gen4	-	-	-	-	-
929000942106	Fortimo LED LLM 4500/740 36W Gen4	-	-	-	-	-
929001410180	Xitanium 15W 0.35A 42V I 230V	-	1.5 mm²	0.2 mm²	-	-
929001417071	Xitanium 10W 0.6A 16V 230V PCB	-	1.5 mm²	0.2 mm²	-	-

Controls and Dimming

Order Code	Full Product Name	Control Input	
		Protection	Control Interface
913700508991	XITANIUM 80W 3.3A 24V 120V 60HZ	-	-
913701214502	XITANIUM 30W 0.52A 60V 0-10V INTELLIVOLT	-	0-10V
913701214602	XITANIUM 39W 0.52A 80V 0-10V INTELLIVOLT	-	0-10V
913701214702	XITANIUM 50W 1.0A 60V 0-10V INTELLIVOLT	-	0-10V
913701215302	Xitanium 150W .35/.41/.53 1-10V 230V sXt	-	1-10V
91370267302	XITANIUM 10W 0.35A 28V 120V 60HZ OUTDOOR	-	-
91370859002	Xitanium 150W 0.70A 230V sXt	-	None
925400009601	OLED Panel Brite FL300 ww B1 PCAL	-	-
925400010101	Driver D024V 10W/0.1-0.4A/28V D/A	-	DALI
925400012002	Driver D024V 10W/0.1-0.4A/28V DMX	-	-
929000636913	XITANIUM 75W 0.7-2.0A 54V TE/ DALI INT	-	DALI/100K
929000637013	XITANIUM 75W 0.7-2.0A 54V TE/ 0-10V INT	-	1-10V Isolated/ 100K
929000645913	InteGrade fixture value 875mm(34") 830	-	-
929000867913	INTEGRATE FIXTURE VISION 875MM(34IN) 830	-	-
929000704913	XITANIUM 75W 0.35-0.70 GL PROG +SD SXT	-	1-10V/AmpDim/ DALI/ Dynadimmer

Order Code	Full Product Name	Control Input	
		Protection	Control Interface
929000705113	XITANIUM 150W 0.35-0.70 GL PROG+SD SXT	-	1-10V/AmpDim/ DALI/ Dynadimmer
929000708113	XITANIUM 2X50W 1.5A 0-10V -H SXT	-	0-10V
929000710403	XITANIUM 100W 0.53A PROG+ GL- Z sXt	-	1-10V/AmpDim/ DALI/ Dynadimmer
929000711213	XITANIUM 54W 0.1-1.5A 27-54V MRK10 120-T	-	Mark 10 dimming
929000711313	XITANIUM 54W 0.1-1.5A 27-54V SD INT-T	-	Step Dimming
929000711413	XITANIUM 75W 0.53A 0-10V INT-Y SXT	-	0-10V
929000711513	XITANIUM 75W 0.53A AOC INT-Y SXT	-	0-10V
929000725113	XITANIUM 75W 1.05A 0-10V INT-Y	-	0-10V
929000805108	Xitanium 40W 0.28A 142V 230V (C)	Yes (Basic insulation)	None
929000814503	Xitanium 36W/0.12-0.4A 110V 230V	Yes (Basic insulation)	-
929000830608	Xitanium 30W 400mA 76V 230V	Yes (Basic insulation)	-
929000866113	InteGrade engine vision 575mm (23") WWR	-	-
929000877403	Fortimo LED DLM 1100 10W/830 UL Gen4	-	-
929000877503	Fortimo LED DLM 1100 10W/835 UL Gen4	-	-

Lumiblade OLED Driver-Low Voltage

Order Code	Full Product Name	Control Input	
		Protection	Control Interface
929000877603	Fortimo LED DLM 1100 9W/840 UL Gen4	-	-
929000877703	Fortimo LED DLM 1500 15W/830 UL Gen4	-	-
929000877803	Fortimo LED DLM 1500 14W/835 UL Gen4	-	-
929000877903	Fortimo LED DLM 1500 13W/840 UL Gen4	-	-
929000878003	Fortimo LED DLM 2000 21W/830 UL Gen4	-	-
929000878103	Fortimo LED DLM 2000 20W/835 UL Gen4	-	-
929000878203	Fortimo LED DLM 2000 19W/840 UL Gen4	-	-
929000878303	Fortimo LED DLM 3000 32W/830 UL Gen4	-	-
929000878403	Fortimo LED DLM 3000 30W/835 UL Gen4	-	-
929000878503	Fortimo LED DLM 3000 29W/840 UL Gen4	-	-

Order Code	Full Product Name	Control Input	
		Protection	Control Interface
929000884406	Xitanium FULL PROG 70W1000 NL1 C150 Xt	-	DynaDimmer
929000941406	Fortimo LED LLM 1100/730 9W Gen4	-	-
929000941506	Fortimo LED LLM 1100/740 8W Gen4	-	-
929000941606	Fortimo LED LLM 1800/730 16W Gen4	-	-
929000941706	Fortimo LED LLM 1800/740 15W Gen4	-	-
929000941806	Fortimo LED LLM 3000/730 26W Gen4	-	-
929000941906	Fortimo LED LLM 3000/740 24W Gen4	-	-
929000942006	Fortimo LED LLM 4500/730 39W Gen4	-	-
929000942106	Fortimo LED LLM 4500/740 36W Gen4	-	-
929001410180	Xitanium 15W 0.35A 42V I 230V	-	None
929001417071	Xitanium 10W 0.6A 16V 230V PCB	-	None

