



The new halogen linear – compact shape, crisp white light

Plusline ES Compact

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires.

Benefits

- Bright, sparkling halogen light to create the right atmosphere
- Fully dimmable, from 0 to 100%, to meet different brightness requirements
- Lower replacement cost due to longer burning hours

Features

- Superior quality of light with excellent color rendering (Ra=100)
- Same size for direct replacement of existing halogen lamps
- Lifetime: 2000 hours
- Universal burning position

Application

- General lighting in shops, restaurants, hotels, galleries, exhibitions and museums.
- Decorative outdoor: billboards, exhibitions and parking areas

Plusline ES Compact

Versions



Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline 78mm 2y 120W R7s 230V 1BB	11 mm	76.5 mm	74.9 mm	73.3 mm	78 mm

